

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced, Metered, 7.4kW, 1Phase, 230V, 32A, 332P6, 40 Outlets

APDU10150ME

⚠ To be discontinued

⚠ Discontinued on: Sep 3, 2025

Overview

Lead time Usually in Stock

Main

Colour Black

Product or component type PDU

PDU type Metered

Cord length 9.8 ft (3.0 m)

Complementary

Input Voltage 230 V 1 phase

Height 58.7 in (1490 mm)

Width 2.2 in (56 mm)

Output Voltage 230 V

Depth 3.0 in (75 mm)

Net weight 13.7 lb(US) (6.2 kg)

Mounting location Side

Mounting preference No preference

Input Plug Type IEC 60309 32 A 2P + PE

Mounting mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication port protocol 1000BASE-T
10/100BASE-T

[In] rated current 32 A

permissible voltage 200...240 V

Input current limits 32 A

Load capacity 7400 VA

Network frequency 50/60 Hz

Outlet type and quantity 20 C13/C15/C19/C21
20C13/C15

Environment

Product certifications	TAA compliance UKCA
Standards	CE EN 62368-1
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	67.7 in (172 cm)
Package 1 Width	4.6 in (11.6 cm)
Package 1 Length	8.2 in (20.8 cm)
Package 1 Weight	18.08 lb(US) (8.2 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	3 174 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	147 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	3 022 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again




Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

Multiple color options available



4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21





