

# Product data sheet

Specifications



## APC NetShelter Rack PDU Advanced, Switched Metered Outlet, 7.4kW, 1Phase, 230V, 32A, 332P6, 40 Outlet

APDU10150SM

! To be discontinued

! Discontinued on: Sep 3, 2025

## Overview

Lead time Usually in Stock

## Main

Colour Black

Product or component type PDU

PDU type Switched metered outlet

Cord length 9.8 ft (3.0 m)

## Complementary

Input Voltage 230 V 1 phase

Height 58.7 in (1490 mm)

Width 2.2 in (56 mm)

Output Voltage 230 V

Depth 3.0 in (75 mm)

Net weight 16.5 lb(US) (7.5 kg)

Mounting location Side

Mounting preference No preference

Input Plug Type IEC 60309 32 A 2P + PE

Mounting mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication port protocol 1000BASE-T  
10/100BASE-T

[In] rated current 32 A

permissible voltage 200...240 V

Input current limits 32 A

Load capacity 7400 VA

Network frequency 50/60 Hz

Outlet type and quantity 20 C13/C15/C19/C21  
20C13/C15

## Environment

<b>Product certifications</b>	UKCA TAA compliance
<b>Standards</b>	CE EN 62368-1
<b>Ambient air temperature for operation</b>	23...140 °F (-5...60 °C)
<b>Relative humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient air temperature for storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0...15240 m)

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	4.528 in (11.500 cm)
<b>Package 1 Width</b>	8.465 in (21.500 cm)
<b>Package 1 Length</b>	67.717 in (172.000 cm)
<b>Package 1 Weight</b>	19.842 lb(US) (9.000 kg)

## Contractual warranty

<b>Warranty (in months)</b>	36
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	2 209 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	170 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 033 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

Multiple color options available



4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21





