

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced, Switched, 3Phase, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309

APDU10350SW

⚠ To be discontinued

⚠ To be discontinued on: Jun 30, 2026

⚠ To be end-of-service on: Jun 30, 2031

Overview

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Switched

Cord length 5.9 ft (1.8 m)

Complementary

Input Voltage 415 V 3 phase
400 V 3 phase

Height 70.08 in (1780 mm)

Width 2.2 in (56 mm)

Output Voltage 240 V

Depth 3.0 in (75 mm)

Net Weight 21.2 lb(US) (9.6 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type IEC 60309 30 A 3P+N+PE

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication Port Protocol 1000BASE-T
10/100BASE-T

Line Rated Current 24 A

permissible voltage 200...240 V
346...415 V

Input current limits 30 A

Load Capacity 17300 VA

Input Frequency 50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	24 C13/C15/C19/C21 24C13/C15
---------------------------------	---------------------------------

Environment

Product Certifications	UKCA TAA compliance BAA compliance
-------------------------------	--

Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
------------------	---

IP Degree of Protection	IP44
--------------------------------	------

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
--	--------------------------

Relative Humidity	5...95 %
--------------------------	----------

Operating altitude	0...10000 ft
---------------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
--	----------------------------

Storage Relative Humidity	5...95 %
----------------------------------	----------

Storage altitude	0...50000 ft (0...15240 m)
-------------------------	----------------------------

Ordering and shipping details

GTIN	731304439721
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
------------------------------	---

Package 1 Height	78.0 in (198 cm)
-------------------------	------------------

Package 1 Width	5.2 in (13.2 cm)
------------------------	------------------

Package 1 Length	10.3 in (26.2 cm)
-------------------------	-------------------

Package weight(Lbs)	27.8 lb(US) (12.6 kg)
----------------------------	-----------------------

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 047 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	70 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 970 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again




Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

Multiple color options available



4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21













