

# Product data sheet

Specifications



## APC NetShelter Rack PDU Advanced, Switched Metered Outlet, 3Phase, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309

APDU10350SM

⚠ To be discontinued

⚠ Discontinued on: Sep 3, 2025

### Overview

Lead time Usually in Stock

### Main

Color Black

Product or Component Type PDU

PDU Type Switched metered outlet

Cord length 5.9 ft (1.8 m)

### Complementary

Input Voltage 415 V 3 phase  
400 V 3 phase

Height 70.08 in (1780 mm)

Width 2.2 in (56 mm)

Output Voltage 240 V

Depth 3.0 in (75 mm)

Net Weight 21.2 lb(US) (9.6 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type IEC 60309 30 A 3P+N+PE

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication Port Protocol 1000BASE-T  
10/100BASE-T

Line Rated Current 24 A

Acceptable Input Voltage 200...240 V  
346...415 V

Input current limits 30 A

Load Capacity 17300 VA

Input Frequency 50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Outlet type and quantity</b>	24 C13/C15/C19/C21 24C13/C15
---------------------------------	---------------------------------

## Environment

---

<b>Product Certifications</b>	UKCA TAA compliance BAA compliance
-------------------------------	--

---

<b>Standards</b>	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
------------------	---

---

<b>IP Degree of Protection</b>	IP44
--------------------------------	------

---

<b>Ambient Air Temperature for Operation</b>	23...140 °F (-5...60 °C)
--	--------------------------

---

<b>Relative Humidity</b>	5...95 %
--------------------------	----------

---

<b>Operating altitude</b>	0...10000 ft
---------------------------	--------------

---

<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
--	----------------------------

---

<b>Storage Relative Humidity</b>	5...95 %
----------------------------------	----------

---

<b>Storage altitude</b>	0...50000 ft (0...15240 m)
-------------------------	----------------------------

## Ordering and shipping details

---

<b>GTIN</b>	731304439745
-------------	--------------

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

---

<b>Nbr. of units in pkg.</b>	1
------------------------------	---

---

<b>Package 1 Height</b>	78.0 in (198 cm)
-------------------------	------------------

---

<b>Package 1 Width</b>	5.2 in (13.2 cm)
------------------------	------------------

---

<b>Package 1 Length</b>	10.3 in (26.2 cm)
-------------------------	-------------------

---

<b>Package weight(Lbs)</b>	27.8 lb(US) (12.6 kg)
----------------------------	-----------------------

## Contractual warranty

---

<b>Warranty (in months)</b>	36
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	2 021 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	226 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 787 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

Multiple color options available



4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21













