

ProductSheet
HP EliteOne 870 G9 All-in-One PC (79D74UA)



Be there even when you're not

The HP EliteOne 870 AiO empowers your team to be at their best with experiences that delight users and IT. Featuring a new sleek design, the latest Intel® processor[2], and packed with a new set of premium collaboration tools, it's ready for all your demanding projects and virtual conferences.



HP Auto Frame

Bring your meetings to life powered by premium audio and video features.[4]

Powerful Intel® processor[2]

Multitask with ease thanks the latest Intel® processor², massive storage, and agile DDR5 memory.

Protected by HP Wolf Security

HP Wolf Security for Business creates a hardware-enforced, always-on, resilient defense.[6]

Featuring

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

HP Sure Sense

Malware is evolving rapidly and traditional antivirus can't always recognize new attacks. Protect your PC against never-before-seen attacks with HP Sure Sense, which uses deep learning AI to provide exceptional protection against advanced malware.

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6. [4]

Protect critical security processes

Keep your critical applications and processes running even if malware tries to shut them down with the self-healing protection of HP Sure Run.

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [6]

Specifications

Form factor	All-in-one
Operating system	Windows 11 Pro ^[1]
Processor family	12th Generation Intel® Core™ i3 processor
Processor	Intel® Core™ i3-12100 (up to 4.3 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 4 cores, 8 threads) ^[6,7]
Chipset	Intel® Q670 (vPro®) ^[3]
Memory	16 GB DDR5-4800 MHz RAM (1 x 16 GB)
Memory Slots	2 SODIMM
Internal Storage	512 GB PCIe® NVMe™ TLC M.2 SSD
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics 730
Display	68.6 cm (27") diagonal, FHD (1920 x 1080), IPS, anti-glare, 250 nits, 72% NTSC
Display	27" diagonal, FHD (1920 x 1080), IPS, anti-glare, 250 nits, 72% NTSC
Audio	Audio by Bang & Olufsen, 5 W stereo speakers, headset and headphone side ports (3.5 mm), high performance integrated stereo speakers
Dimensions (W x D x H)	61.4 x 24.7 x 59.95 cm
Dimensions (W x D x H)	24.17 x 9.72 x 23.6 in
Weight	11.6 kg (Exact weight depends on configuration.)
Weight	25.57 lb (Exact weight depends on configuration.)
Package dimensions (W x D x H)	74.2 x 23.7 x 64.0 cm
Package dimensions (W x D x H)	29.21 x 9.33 x 25.20 in
Package weight	15.07 kg
Package weight	33.22 lb
Keyboard	HP Wired Desktop 320K Keyboard
Pointing device	HP 125 Wired Mouse
Camera	5 MP Swivel IR camera for face authentication with Windows Hello with integrated dual array digital microphones and Color Light Sensor; 5 MP Swivel camera with temporal noise reduction and integrated dual array digital microphones; 16 MP binning Swivel IR camera for face authentication with Windows Hello with Color Light Sensor and Time of Flight Sensor ^[11]
Ports	1 headphone/microphone combo
Expansion slots	1 M.2 2230; 3 M.2 2280 (1 M.2 2230 slot for WLAN and Bluetooth® combo. 3 M.2 2280 for NVMe SSD for storage one attached to CPU PCIe Gen 4.0 and two attached to PCH PCIe Gen 3.0)
Ports	1 USB Type-C® 20Gbps signaling rate (charging); 1 USB Type-A 10Gbps signaling rate
Ports	1 USB Type-C® 10Gbps signaling rate (DisplayPort™ 1.4); 2 USB Type-A 10Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 1 HDMI-in 1.4; 1 dual-mode DisplayPort™ 1.4; 1 RJ-45
Network interface type	WLAN
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card (supporting gigabit data rate)
Energy star certified	ENERGY STAR® certified
Management features	HP Client Catalog (download); HP Driver Packs (download); HP Image Assistant (download); HP Client Management Script Library (download); HP Connect for Microsoft Endpoint Manager; HP Manageability Integration Kit (download); HP Patch Assistant (download); HP CECF Enabled Configuration ^[12,13,14]
Sustainable impact specifications	Ocean-bound plastic in speaker enclosure; 40% post-consumer recycled plastic; 30% ITE-derived closed loop plastic; Low Halogen; 80 Plus® Platinum power supplies available
Security management	Trusted Platform Module TPM 2.0 Embedded Security Chip shipped with Windows 10 (Common Criteria EAL4+ Certified)(FIPS 140-2 Level 2 Certified); HP Sure Start; HP Secure Erase; HP Sure Click; HP Sure Sense; Absolute Persistence module; HP Sure Admin; HP BIOSphere Gen6; HP Client Security Manager Gen7; HP Tamper Lock; HP Sure Run Gen6; HP Sure Recover Gen6; HP Platform Certificate; Seamless Firmware Update Service; Secured-CORE PC Disable; Windows Hello Enhanced Sign-in Security (ESS) Enable ^[19,20,21,22,23,24,25,26,27,28]
Software included	HP Notifications; HP PC Hardware Diagnostics UEFI; HP Support Assistant; HP Connection Optimizer; HP Privacy Settings; HP PC Hardware Diagnostics Windows; HP Desktop Support Utilities; MyHP; HP QuickDrop; HP Easy Clean; Touchpoint Customizer for Commercial; HP Easy Clean Keyboard Driver; HSA Fusion for Commercial; HSA Telemetry for Commercial ^[15,16,17]

UPC number	197029831293
------------	--------------

Top Recommended Displays, Accessories and Services

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA

Speakerphones

Poly Sync 10 USB-A USB-C Speakerphone	772C3AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 20+ USB-C Speakerphone	772D0AA

Wireless Headset

Poly Voyager 4320 USB-C Headset +BT700 dongle	76U50AA
---	---------

Mounting Brackets

HP EliteOne G9 VESA Plate	6H1W8AA
HP Quick Release Bracket 2	6KD15AA

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[4] Requires Windows 11 OS.

[4] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[6] HP Wolf Security for Business requires Windows 10 or 11 Pro and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features and OS requirements.

[6] HP Sure Click supports Microsoft® Internet Explorer and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[3] For full Intel® vPro® functionality, Windows 11 Pro 64 bit, a vPro supported processor, vPro enabled chipset, vPro enabled wired LAN and/or WLAN card and TPM 2.0 are required. Some functionality requires additional 3rd party software in order to run. See <http://intel.com/vpro>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[11] Sold separately or as an optional feature.

[12] HP Connect for Microsoft Endpoint Manager is available from the Azure Market Place for HP Pro, Elite, Z and Point-of-Sale PCs managed with Microsoft Endpoint Manager. Subscription to Microsoft Endpoint Manager required and sold separately. Network connection required.

[13] HP Patch Assistant available on select HP PCs with the HP Manageability Kit that are managed through Microsoft System Center Configuration Manager. HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>.

[14] HP Manageability Integration Kit can be downloaded from <http://www.hp.com/go/clientmanagement>.

[15] myHP requires Windows OS.

[16] HP Quick Drop requires Internet access and Windows 10 or higher PC preinstalled with HP QuickDrop app and either an Android device (phone or tablet) running Android 7 or higher with the Android HP QuickDrop app, and /or an iOS device (phone or tablet) running iOS 12 or higher with the iOS HP QuickDrop app.

[17] HP Support Assistant requires Windows and Internet access.

[19] HP Sure Click requires Windows 10 Pro or higher or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[20] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

[21] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[22] HP Sure Recover Gen5 with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.

[23] HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.

[24] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

[25] HP Client Security Manager Gen7 requires Windows and is available on the select HP Elite and Pro PCs.

Learn more at
hp.com

[26] HP BIOSphere Gen6 features may vary depending on the platform and configuration.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel®, the Intel logo, Intel Core, vPro®, Optane™, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth® is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. AMD is a trademark of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

