

HP ProOne 240 G10 Desktop PC (B8SU2AT)



All-in-One value, all in one PC

The HP ProOne 240 All-in-One provides power and features for productivity and business-grade performance. A great value, with up to an Intel® Core™ Ultra 7 processor[2,4] which features a neural processing unit (NPU) for AI[4,5] a 23.8-inch Full HD display[3], video-enhancement features in a sleek, stylish design, and tiltable camera.[7]



Adapted for today's work

Set yourself up for success with powerful performance and enhanced video features—all-in-one design.

Remarkable tech

Get the latest technology at a great value with a powerful Intel® processor.[2,4]

Sleek, professional design

Equipped with a three-sided micro-edge display, this slim, stylish All-in-One frees space on your desk.

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [1]

13th Gen Intel® multi-core processor

Get the perfect combination of power, snappy performance, and value with a 13th gen Intel® Core™ processor to handle multiple work tasks smoothly and reliably with multiple processing cores. [2]

Enjoy a clutter-free desk

The smart design features in this sleek AiO let you manage your workspace efficiently. Quick and easy access to ports and optional wireless Wi-Fi 6 with Bluetooth® helps reduce cord clutter.

Simple PC management

Spend less time and get right to the updates you need with HP Support Assistant. [4]

Specifications

Form factor	All-in-one
Operating system	Windows 11 Pro
Processor family	13th Generation Intel® Core™ i5 processor
Processor	Intel® Core™ i5-1334U (up to 4.6 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 10 cores, 12 threads) [6,7]
Memory	16 GB DDR4-3200 MT/s (1 x 16 GB)
Memory Slots	2 SODIMM
Internal Storage	512 GB PCIe® NVMe™ SSD
Internal drive bays	One 2.5" HDD
Graphics	Integrated
Graphics (integrated)	Intel® Iris® X ^e Graphics
Display	60.5 cm (23.8") diagonal, FHD (1920 x 1080), IPS, three-sided micro-edge, anti-glare, 250 nits, 72% NTSC
Display	23.8" diagonal, FHD (1920 x 1080), IPS, three-sided micro-edge, anti-glare, 250 nits, 72% NTSC
Audio	Realtek ALC3274 codec, high performance internal speaker, combo microphone/headphone jack, line-in and line-out rear ports (3.5 mm)
Dimensions (W x D x H)	54.06 x 18.37 x 41.9 cm
Dimensions (W x D x H)	21.28 x 7.23 x 16.50 in
Weight	5.37 kg
Weight	11.84 lb
Keyboard	HP 125 USB Wired Keyboard
Pointing device	HP 125 Wired Mouse
Camera	5 MP camera (pull-up) with integrated dual array digital microphones
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 2 USB 2.0 Type-A; 1 HDMI 1.4; 1 headphone/microphone combo; 1 RJ-45; 1 power connector
Expansion slots	1 M.2 2230; 1 M.2 2280; 1 SATA storage connector (1 M.2 slot for WLAN and 1 M.2 2280 slot for storage.)
Package dimensions (W x D x H)	64.1 x 27.7 x 52.5 cm
Package weight	8.5 kg
Wireless	Realtek Wi-Fi 6 (1x1) and Bluetooth® 5.3 wireless card
Power	90 W external power adapter
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low Halogen
Software included	HP PC Hardware Diagnostics UEFI; HP Support Assistant; HP JumpStarts; HP Cloud Recovery ^[10,11,12]
UPC number	198990565309

Top Recommended Displays, Accessories and Services

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	93S88AA
Poly Blackwire 3325 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X221AA
Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	8X228AA
Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	93S87AA

Speakerphones

Poly Sync 10 USB-A USB-C Speakerphone	772C3AA
---------------------------------------	---------

Wireless Headset

Poly Voyager 4320 USB-C Headset +BT700 dongle	76U50AA
---	---------

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Full high-definition (FHD) content required to view FHD images.

[4] Internet access required.

[5] Eye Contact, Background Blur, and Automatic Framing are Windows Studio Effects features that require Windows 11 OS and a processor equipped with an NPU. AI features may require software purchase, subscription, or enablement by a software platform provider, or may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[11] HP Cloud Recovery is available for HP Elite and Pro desktops and laptops PCs with Intel® or AMD processors and requires an open, wired network connection. Note: You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Detail please refer to: <https://support.hp.com/us-en/document/c05115630>.

[12] Simply sign up and start using Xerox® DocuShare® Go. No credit card. No obligation. Data will become unavailable unless a subscription is entered before the end of the 90 day free trial period. See visit www.xerox.com/docusharego for details.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

