

# HP Z8 Fury G5 Workstation (A32RPUA)



## Extreme performance. Infinite possibilities

Experience a new echelon in high performance. Transformative single socket technology delivers extreme performance with up to 56 cores in a single CPU, to also unleash the power of up to 4 high-end GPUs. Now you can breeze through even the most complex deep learning, virtual production, and VFX.



HP recommends Windows 11 Pro for business

### Relentless power. Extraordinary expandability

Tackle the most complex workflows with the latest Intel® Xeon® CPU[1], high-end GPUs, and extraordinary amounts of memory, storage, and power. Easily expand as work evolves with next gen PCIe slots, front accessible NVMe bays, and tool-less access.

### Engineered to stay cool and quiet

Stay focused. Smart fan control keeps your PC whisper-quiet by tuning fan speeds using 20 temperature sensors.

### Comprehensive security. Reliability you can trust

Trust the 360K hours of testing, certifications for pro apps, and world-class HP Wolf Security for Business[12].

## Featuring

### Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

### Intel® Xeon® W processor

Get optimized performance whether your professional application utilizes high core count or high frequency with the Intel® Xeon® W processor. [1]

### Professional Grade Graphics

Tackle complex renderings, simulations and datasets with professional grade graphics.

# Specifications

|                                   |                                                                                                                                                                                                                                                                                                                                                              |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Form factor                       | Tower                                                                                                                                                                                                                                                                                                                                                        |
| Operating system                  | Windows 11 Pro <sup>[1]</sup>                                                                                                                                                                                                                                                                                                                                |
| Processor family                  | Intel® Xeon® W processor                                                                                                                                                                                                                                                                                                                                     |
| Processor                         | Intel® Xeon® W9-3495X (up to 4.8 GHz with Intel® Turbo Boost Technology, 105 MB L3 cache, 56 cores, 112 threads) [6,7]                                                                                                                                                                                                                                       |
| Chipset                           | Intel® W790                                                                                                                                                                                                                                                                                                                                                  |
| Memory                            | 128 GB DDR5-4800 MHz RAM (4 x 32 GB)                                                                                                                                                                                                                                                                                                                         |
| Memory Slots                      | 16 DIMM                                                                                                                                                                                                                                                                                                                                                      |
| Internal Storage                  | 2 TB HP Z Turbo Drive PCIe® NVMe™ TLC M.2 SSD                                                                                                                                                                                                                                                                                                                |
| Internal drive bays               | Six PCIe® M.2 SSD; Six 3.5" HDD                                                                                                                                                                                                                                                                                                                              |
| External drive bays               | Four NVMe™ M.2 SSD; Two 3.5" HDD; Two 9.5 mm ODD                                                                                                                                                                                                                                                                                                             |
| Graphics                          | Discrete                                                                                                                                                                                                                                                                                                                                                     |
| Graphics (discrete)               | NVIDIA RTX™ A2000 (6 GB GDDR6 dedicated)                                                                                                                                                                                                                                                                                                                     |
| Compatible displays               | All HP Z Displays and HP DreamColor Displays are supported. For more information see <a href="http://www.hp.com/go/zdisplays">http://www.hp.com/go/zdisplays</a>                                                                                                                                                                                             |
| Audio                             | Realtek ALC3205-CG                                                                                                                                                                                                                                                                                                                                           |
| Minimum dimensions (W x D x H)    | 21.59 x 55.12 x 44.45 cm                                                                                                                                                                                                                                                                                                                                     |
| Weight                            | Starting at 22 kg<br>(Exact weights depend upon configuration (System weight only))                                                                                                                                                                                                                                                                          |
| Keyboard                          | HP USB 320K Keyboard                                                                                                                                                                                                                                                                                                                                         |
| Pointing device                   | HP Wired 320M Mouse                                                                                                                                                                                                                                                                                                                                          |
| Expansion slots                   | 1 PCIe 3 x8; 2 PCIe 5 x16; 1 PCIe 5 x4; 2 PCIe 4 x16; 2 PCIe 4 x4; 2 PCIe 4 x8<br>(Rear bulkhead access can be achieved through all slots but 2 PCIe 4 x8 are internal access only for M.2.)                                                                                                                                                                 |
| Ports                             | 2 USB Type-C® 20Gbps signaling rate (USB Power Delivery); 2 USB Type-A 5Gbps signaling rate; 1 headphone/microphone combo                                                                                                                                                                                                                                    |
| Package dimensions (W x D x H)    | 33.2 x 73.4 x 63.6 cm                                                                                                                                                                                                                                                                                                                                        |
| Package weight                    | Starting at 27.95 kg                                                                                                                                                                                                                                                                                                                                         |
| Power                             | 2250 W aggregate internal power supply, up to 90% efficiency, active PFC; 1450 W internal power supply, up to 90% efficiency, active PFC; 1450 W redundant internal power supply, up to 90% efficiency, active PFC; 1125 W internal power supply, up to 90% efficiency, active PFC; 1125 W redundant internal power supply, up to 90% efficiency, active PFC |
| Management features               | HP Driver Packs; HP System Software Manager (download); HP BIOS Configuration Utility (download); HP Smart Support                                                                                                                                                                                                                                           |
| Sustainable impact specifications | Low Halogen; 40% post-consumer recycled plastic; 25% ITE-derived closed loop plastic; Bulk packaging available; External power supply 90% efficiency; Plastic cushion inserts contain 80% recycled content; Ocean-bound plastic in system fan; 10% post-industrial recycled metal                                                                            |
| Security management               | Full volume encryption; HP Secure Erase; Kensington lock slot; Secure authentication; TPM 2.0 certified; HP BIOSphere; HP Sure Run; HP Sure Click; HP Sure Sense; HP Sure Admin; HP Platform Certificate; HP Sure Start; HP Sure Recover; Self-Encrypted Drives <sup>[20,21,22,23,24,25,26,27]</sup>                                                         |
| Software included                 | HP PC Hardware Diagnostics UEFI; HP Performance Advisor; HP Support Assistant; HP PC Hardware Diagnostics Windows; HP Image Assistant; HP Manageability Integration Kit; HP Anyware; HP Services Scan; HP Data Science Stack Manager <sup>[17,18,19,32,33]</sup>                                                                                             |
| UPC number                        | 198415075321                                                                                                                                                                                                                                                                                                                                                 |

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[12] HP Wolf Security for Business requires Windows 10 or 11 Pro or higher, includes various HP security features and is available on HP Pro, Elite and Workstation products. See product details for included security features.

## Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[17] HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www8.hp.com/us/en/workstations/performance-advisor.html>.

[18] HP Support Assistant requires Windows and Internet access.

[19] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>.

[20] HP Sure Click requires Windows 11 Pro or Enterprise. See [https://bit.ly/2PrLT6A\\_SureClick](https://bit.ly/2PrLT6A_SureClick) for complete details.

[21] HP Sure Start Gen7 is available on select HP PCs and Workstations. See product specifications for availability.

[22] HP Sure Recover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP Sure Recover to avoid loss of data.

[23] HP Sure Sense requires Windows 11 Pro or Enterprise and supports Microsoft Internet Explorer, Google Chrome™, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[24] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[25] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

[26] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88.

[27] HP BIOSphere Gen6 features may vary depending on the platform and configurations.

[32] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit <http://www.hpdaas.com/requirements>. Not applicable in China.

[33] HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www.hp.com/us-en/workstations/performanceadvisor.html>.

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA is trademark and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® is registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

