

HP ProBook 440 14 inch G11 Notebook PC (A45RSPT)



Performance to stay productive from anywhere

The HP ProBook 440 14-inch laptop provides growing businesses with commercial-grade performance, multi-layered endpoint security[4], and durability in an easily upgradeable design. Powered by the latest Intel® processor[2] and long battery life, this feature-rich PC is well-equipped for long-term productivity and helps enable hybrid work.



HP recommends Windows 11 Pro for business

Designed for hybrid productivity

Enhance productivity working from home or in the office with the 16:10 aspect ratio on a 14-inch display.

Latest Intel® processor

Keep up with demanding, deadline-driven tasks with the latest Intel® processor[2] and long battery life.

Enterprise-level security

Safeguard your growing business with multi-layered, endpoint security features[4] that help protect your PC and data.

Featuring

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Latest Intel® multi-core processor

Configure your HP ProBook CPU for the perfect combination of power, snappy performance, and value. The latest Intel® processor handles multiple work tasks smoothly and reliably with multiple processing cores to divide up the work. [2]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6. [1]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [3]

HP Sure Sense

Malware is evolving rapidly and traditional antivirus can't always recognize new attacks. Protect your PC against never-before-seen attacks with HP Sure Sense, which uses deep learning AI to provide exceptional protection against advanced malware.

Specifications

Operating system	Windows 11 Pro
Product color	Pike silver
Processor family	Intel® Core™ Ultra 7 processor
Processor	Intel® Core™ Ultra 7 155U (up to 4.8 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 12 cores, 14 threads) [6,7]
Processor technology	Intel® vPro® Technology
Memory	16 GB DDR5-5600 MHz RAM (2 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® Graphics
Display	35.6 cm (14") diagonal, WUXGA (1920 x 1200), IPS, narrow bezel, anti-glare, 300 nits, 45% NTSC
Display	14" diagonal, WUXGA (1920 x 1200), IPS, narrow bezel, anti-glare, 300 nits, 45% NTSC [15,16,17,18,38]
Display size (diagonal)	35.6 cm (14")
Display size (diagonal)	14"
Audio	Audio by Poly Studio, dual stereo speakers with discrete amplifiers, integrated dual array microphones
Minimum dimensions (W x D x H)	31.86 x 22.44 x 1.09 cm (front); 31.86 x 22.43 x 1.7 cm (rear) (Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)
Minimum dimensions (W x D x H)	12.54 x 8.83 x 0.43 in (front); 12.54 x 8.83 x 0.67 in (rear) (Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)
Weight	Starting at 1.39 kg (Weight will vary by configuration. Does not include power adapter.)
Weight	Starting at 3.08 lb (Weight will vary by configuration. Does not include power adapter.)
Keyboard	Spill-resistant, optional backlit keyboard with DuraKeys
Pointing device	Clickpad with multi-touch gesture support
Ports	2 USB Type-C® 20Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4, HP Sleep and Charge); 2 USB Type-A 5Gbps signaling rate (1 charging, 1 power); 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45 (HDMI cable sold separately.)
Package dimensions (W x D x H)	6.9 x 44.9 x 30.5 cm
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card (supporting gigabit data rate)
Power	65 W USB Type-C™ adapter [38]
Battery type	HP Long Life 3-cell, 56 Wh Li-ion
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 20% post-consumer recycled plastic; Ocean-bound plastic in speaker enclosure and system fan; 50% recycled metal
UPC number	198415237071
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

E-Series

HP E24 G5 FHD Monitor	6N6E9AA
-----------------------	---------

P-Series

HP P27h G5 FHD Monitor	64W41AA
HP P24h G5 FHD Monitor	64W34AA

Speakerphones

Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 10 USB-A USB-C Speakerphone	772C3AA

Wireless Headset

Poly Voyager 4320 USB-C Headset +BT700 dongle +Charging Stand	77Z31AA
---	---------

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 3320 Stereo USB-C Headset +USB-C/A Adapter	8X219AA

Topload Bags

HP Prelude 15.6-inch Laptop Bag	2Z8P4AA
HP Prelude 15.6-inch Topload	1E7D7AA
HP Prelude 15.6-inch Topload	50P31AA
HP Renew Business 14.1-inch Laptop Bag	3E5F9AA

Backpacks

HP Prelude Pro 15.6-inch Recycled Backpack	1X644AA
HP Renew Business 17.3-inch Laptop Backpack	3E2U5AA

Wired Keyboards

HP Wired Desktop 320K Keyboard	9SR37AA
--------------------------------	---------

Wireless Keyboards

HP 225 Wireless Keyboard	805T1AA
HP 455 Programmable Wireless Keyboard	4R177AA

Wired Mice

HP Wired Desktop 320M Mouse	9VA80AA
-----------------------------	---------

Wireless Mice

HP 235 Slim Wireless Mouse	4E407AA
HP 435 Multi-Device Wireless Mouse	3B4Q5AA

Port Replicators

HP Universal USB-C Multiport Hub	50H55AA
HP USB-C Travel Hub G3	86S97AA

Power Adapters

HP 65W GaN USB-C Laptop Charger	600Q7AA
HP 65W GaN USB-C Laptop Charger	600Q8AA
HP 65W USB-C LC Power Adapter	1P3K6AA
HP 65W USB-C LC Power Adapter	944V0AA
HP 45W USB-C LC Power Adapter	1MZ01AA

Messaging Footnotes

[1] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] HP Sure Click supports Microsoft® Internet Explorer and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[4] HP Wolf Security for Business requires Windows 10 and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features and OS requirements.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[15] WQXGA/WUXGA/FHD resolution content required to view WQXGA/WUXGA/FHD images.

[16] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[17] Actual brightness will be lower with touchscreen.

[18] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[38] Availability may vary by country.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Ultra and Arc are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. NVIDIA, the NVIDIA logo are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

