# Product data sheet

Specifications



## APC NetShelter SX Server Rack Gen 2, 42U, 1991H x 600W x 1200D mm, with Sides, Black [TAA]

AR3300B2

## Overview

| | |
|---|---|
| **Lead time** | Usually in Stock |

## Main

| | |
|---|---|
| **Product or Component Type** | Rack enclosure |
| **Number of rack unit** | 42U |
| **Provided equipment** | Baying hardware<br>Key(s)<br>Keyed-alike doors and side panels<br>Leveling feet<br>Mounting Hardware<br>Pre-installed casters<br>Side Panels |

## Physical

| | |
|---|---|
| **Height** | 78.4 in (1991 mm) |
| **Width** | 23.6 in (600 mm) |
| **Depth** | 47.2 in (1200 mm) |
| **Net Weight** | 288.89 lb(US) (131.04 kg) |
| **Color** | Black |
| **Mounting preference** | No preference |
| **Mounting Mode** | Not rack-mountable |
| **Maximum Mounting Depth** | 41.3 in (1048 mm) |
| **Minimum Mounting Depth** | 7.5 in (190.5 mm) |
| **Rack Width** | 19" |
| **Marking** | 14 gauge EIA mounting rail<br>16 gauge front door<br>16 gauge post<br>18 gauge rear door<br>18 gauge roof<br>18 gauge side panels |
| **Permanent permissible load** | 2250 lb(US) (1020.6 kg) dynamic<br>4000 lb(US) (1814.4 kg) static |

## Conformance

| | |
|---|---|
| **Standards** | UL 2416<br>EIA-310E |

## Ordering and shipping details

| | |
|---|---|
| **GTIN** | 731304642206 |

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---|---|
| **Country of origin** | CN |

## Packing Units

| | |
|---|---|
| **Unit Type of Package 1** | PCE |
| **Nbr. of units in pkg.** | 1 |
| **Package 1 Height** | 83.8 in (212.8 cm) |
| **Package 1 Width** | 29.4 in (74.8 cm) |
| **Package 1 Length** | 52.09 in (132.3 cm) |
| **Package weight(Lbs)** | 328.69 lb(US) (149.09 kg) |

## Compliance

| | |
|---|---|
| **Compliance** | TAA Compliant<br>BAA Compliant via COTS |

## Contractual warranty

| | |
|---|---|
| **Warranty (in months)** | 60 |

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### Environmental footprint

| | |
|---|---|
| Total lifecycle Carbon footprint | **1 168 kg CO2 eq.** |
| Carbon footprint of the manufacturing phase [A1 to A3] | **796 kg CO2 eq.** |
| Carbon footprint of the distribution phase [A4] | **44 kg CO2 eq.** |
| Carbon footprint of the installation phase [A5] | **17 kg CO2 eq.** |
| Carbon footprint of the use phase [B2, B3, B4, B6] | **0 kg CO2 eq.** |
| Carbon footprint of the end-of-life phase [C1 to C4] | **357 kg CO2 eq.** |
| Environmental Disclosure | Product Environmental Profile |

## Use Better

### Materials and Substances

| | |
|---|---|
| Packaging made with recycled cardboard | **No** |
| Packaging without single use plastic | **No** |
| EU RoHS Directive | Compliant |
| REACh Regulation | Free of Substances of Very High Concern above the threshold |

## Use Longer

### Lifetime extension

| | |
|---|---|
| Repair | **No** |

## Use Again

### Repack and remanufacture

| | |
|---|---|
| Recyclability potential, in % | **97** |
| Circularity Profile | **No need of specific recycling operations** |
| Take-back | **No** |

Technical Illustration

**Dimensions**



Image of product / Alternate images

**Alternative**







