



See page 2 for specifications / Jumbo Mount compatibility.

ALL DIMENSIONS: $\frac{\text{INCH}}{\text{MM}}$ C = CENTER LINE TYP. = TYPICAL



ASSEMBLY VIEW

Jumbo Mount TV/Monitor Mount attaches to wall arm as shown. Flush mount tube, fiber washers, and retaining collar are included with Jumbo Mount.



Architects specifications:

The Wall Arm shall be a Peerless model WMJ018(S) & WMJ022(S) and shall be attached where indicated on the plans. It shall have a 1 1/2 - 11.5 NPS threaded fitting to accept a Peerless flush mount tube. It shall be constructed of 12 and 14 gauge cold rolled steel and finished in black or silver fused epoxy. Assembly and installation shall be done according to the instructions provided by the manufacturer.

**TECHNICAL DATA SHEET
WALL ARM FOR JUMBO MOUNTS**

Peerless-AV

2300 White Oak Circle
Aurora, IL 60502, USA


phone: (800)865-2112
fax: (630)375-5100

ISSUED: 1995-03-08 SHEET NO:128-9503-3 (2025-09-08)

WALL ARM FOR JUMBO MOUNTS - SPECIFICATIONS						
Weight	Shipping Weight	Model Number	Reach	Max. Load Capacity		Compatible Jumbo Mount Models
				Concrete	Wood	
9.4 lb (4.3 kg)	12 lb (6 kg)	WMJ018	18" (457 mm)	150 lb (68 kg)	125 lb (57 kg)	JM 2630, JM 2640, JM 2640D
10.2 lb (4.6 kg)	13 lb (6 kg)	WMJ018S WMJ022 WMJ022S	22.5" (571 mm)	150 lb (68 kg)	125 lb (57 kg)	JM 2630, JM 2630S, JM 2640, JM 2640S, JM 2640D, JM 2640DS, JM 2650, JM 2650S, JM 2650D, JM 2650DS, JM 2655, JM 2655S

Reach

WARNING: WEIGHT OF TV or MONITOR NOT TO EXCEED MAXIMUM LOAD CAPACITY!



Wall Arms include three wood screws and plastic sleeves (left) for attachment to a wood stud wall. For attachment to a concrete wall additional fastener package **ACC210** must be ordered.

