

MX 2.0S

Made for gaming – a functional, state-of-the-art keyboard featuring MX technology



Models may vary from the image shown

The CHERRY MX 2.0S – the functional, classic keyboard that has everything you need for gaming. The streamlined German design concentrates on functionality, using the Bauhaus principle as its basis. Designed by Prof. Peter Raab, lecturer at Coburg University, the exterior and interior have been optimized.

The interior features the time-tested mechanical CHERRY MX technology and provides a choice of different switching characteristics. Special Gold Crosspoint contacts ensure consistently reliable electrical contacts, perfect responsiveness, and an unbeatable reaction speed. Multiple mechanical components under each key ensure a uniform feel.

Now available with CHERRY MX2A switches. The world's most trusted mechanical keyboard switch just got better. CHERRY MX2A is a transformative upgrade to the CHERRY MX – used in more than 60 million keyboards worldwide. With precisely applied premium-grade lubricant and a new innovative spring design, the MX2A brings you smoother actuation, improved acoustics, and a lifespan of up to 100 million keystrokes.

Depending on the model, without lighting or with vivid RGB lighting effects in more than 16 million

colors. A variety of plays of color, lighting modes and key assignments can be managed using the free CHERRY Utility software.

A matching palm rest is available as an optional accessory to provide more comfort. High-quality workmanship and abrasion-resistant key caps provide unfailing reliability when gaming, at home, and at work.

HIGHLIGHTS

- Classic, wired keyboard with original CHERRY MX switches
- Impressive RGB lighting in more than 16 million colors, with numerous integrated color routines, which can also be adjusted using the CHERRY Utility Software (depending on the version)
- CHERRY MX technology – Gold Crosspoint precision switches for all keys »Made in Germany«
- Minimalist, functional design – designed in Germany by Prof. Peter Raab
- Uniform feel across all keys due to special, multiple mechanical components
- Full n-key rollover – all keys are read simultaneously
- Anti-ghosting – no input errors
- WIN key lockout
- CHERRY key for quick access to Utility software
- Abrasion-resistant, laser-etched key caps
- Available in different MX switching characteristics
- Matching palm rest available as an optional accessory

PRODUCT SPECIFICATIONS

Colour:	black
Weight main product:	29 oz
Weight of product without packaging:	29.45 oz

Weight of product incl. packaging: 39.86 oz

Weight of master carton incl. content: 335.1 oz

Content of master carton (pieces): 8

Dimensions product without packaging: 16,97 in x 5,67 in x 1,42 in

Dimensions product incl. packaging: 17,72 in x 9,06 in x 1,69 in

Dimensions master carton: 18.5 in x 15.35 in x 8.66 in

Cable length: 5.91 ft

Storage temperature: -4 °F - 140 °F

Working temperature: 32 °F - 122 °F

Product approvals:

- China RoHS
- CE
- KCC
- Windows Hardware Compatibility
- BSMI
- FCC
- RCM
- UKCA

System Requirements-Hardware: USB-A

Operating system:

- Windows 7
- Windows 8
- Windows 10
- Windows 11

Scope of delivery:

- Short Manual
- Keyboard

Software support: CHERRY Utility Software & Assistant

Service life per key (in million strokes): 100 mio. actuations

Switching characteristics: linear

Max. current consumption (mA) of keyboard: 500 mA

Keyboard format: Full-size (100%)

Integrated metal plate: no

N-Key Rollover: yes

Anti-ghosting: yes

Key encryption: no

Response time: 1 ms

Internal memory: no

Actuating force (cN): 45 cN

Pre-Travel: 2 mm

Total Key Travel: 4 mm

Key labeling: Laser etching + UV coating

Palm rest: Palm rest available as accessory

USB-Hub: no

Number of keys: 105 + 4

Special key functions:

- Browser
- CHERRY Key
- FN
- Next track
- Last track
- Play/Pause
- Unmute/Mute
- Volume up
- Volume down
- Calculator

Illumination: RGB

Adjustable feet: integrated

Status LEDs: in keys

Key technology: Mechanical

Switches: CHERRY MX2A RED

Keycap material: ABS

EAN: 4025112113260

UPC: 840183607821

Model number: G80-3821

Protection class: Standard

Hotswap: no

Warranty: 2 years warranty

Layout: US (USA)

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.