



## SEAL CLEAN™ WATERPROOF KEYBOARD

**Model:** SSKSV207, SSWKSV207, SSKSV207L, SSWKSV207L

### TECHNICAL DATA:

Compatibility:	Windows®
Construction:	ABS Plastic (Standard Style)
Net Dimensions L x W x H:	18.07 x 6.85 x 1.38 in (45.9 x 17.4 x 3.5 cm)
Key Layout:	104 US Language
Net Weight:	207: 1.93 lb (0.875 kg) 207L: 1.87 lb (0.850 kg)
Gross Weight:	207: 2.31 lb (1.050 kg) 207L: 2.26 lb (1.025 kg)
Cable Length:	SSKSV207L, SSWKSV207L: 6 ft.(1.83m) USB Extension Cable SSKSV207, SSWKSV207: 6in (15cm) Quick Connect Cable with 6 ft.(1.83m) USB Extension Cable
Connection Type:	Gold Plated USB (can support PS/2 technology)
Key Switch Force:	53 ± 7 gf
Key Switch Life Cycle:	Greater Than 10 Million Keystrokes
Key Switch Type:	Membrane Key Switch with Tactile Feedback
Keycaps Imaging Type:	Laser Etched
Total Key Travel:	4.0 ± 0.2mm
Operating Current:	60mA
Operating Voltage:	5VDC
Storage Temperature:	-5° - 140° F (-20° to 60° C)
EMI - RFI:	Conforms to FCC Rules for Class B Computing Device
Waterproof/Dustproof Ratings:	IP68, NEMA 4X
Approvals/Certifications:	FCC, CE, RoHS, WEEE, WHQL, ICES-003, EAC, KC, RCM, and cULus, REACH, Cal Prop 65



Copyright© 2022, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners.

Limited 2-Year Warranty