Product data sheet

Specifications



Dry contact, Management Options, Dry Contact I/O Card, monitor external UPS environmental sensors, output relays, and input contacts

AP9614

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time	Usually in Stock

Main

Range of Product	Management Options and Cables
Provided Equipment	User Manual USB cable
Product or Component Type	Dry contact
Number of rack unit	0U
Cable length	0.522 ft (0.159 m)
Rated voltage	24 V
Line Rated Current	0…200 mA

General

Power supply type	Self powered via SmartSlot

Physical

Height	1.5 in (3.8 cm)
Width	4.8 in (12.1 cm)
Depth	5.04 in (12.8 cm)
Net Weight	0.44 lb(US) (0.20 kg)
Mounting Mode	Not rack-mountable

Conformance

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-6 FCC Part 15 class A FCC CFR 47 part 15 EN 61000-6-3 (2007) BS EN 61000-6-3 EN 55032 BS EN 55032 VCCI class A CISPR 32 EN/IEC 61000-3-2 AS/NZS CISPR 32 EN 61000-6-1 (2007) EN 55035 BS EN 55024 IEC 62040-2 BS EN 62040-2 EN 61326-2 BS EN 61326-2 BS EN 61000-4-2 BS EN 61000-4-3 BS EN 61000-4-4 EN 61000-4-5 BS EN 61000-4-5 BS EN 61000-4-6 EN 61000-4-8 BS EN 61000-4-8 EN 61000-4-11 BS EN 61000-4-11 BS EN 55035 EN 62040-2 ICES-003 class A EN 61000-6-3 BS EN 61000-3-2 BS EN 61000-3-3 AS/NZS EN 61000-3-2:2023 AS/NZS EN 61000-3-3:2023

Environmental

Ambient Air Temperature for Operation	32…104 °F (0…40 °C)
Operating altitude	0...10000 ft 0...50000 ft
Ambient Air Temperature for Storage	5…149 °F (-15…65 °C)
Storage altitude	0…50000 ft (0…15240 m)

Ordering and shipping details

GTIN	731304733065

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.008 in (5.1 cm)
Package 1 Width	6.5 in (16.5 cm)
Package 1 Length	9.4 in (23.8 cm)
Package weight(Lbs)	15.5 oz (440 g)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**270 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**5 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**265 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**0 kg CO2 eq.**
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**95**
Circularity Profile	End of Life Information
Removable battery	**No**
Take-back	**Nej**

Image of product / Alternate images

Alternative




Universal I/O
1
2
USB
Status
RESET
ON
STARTING
COM ERROR
FAULT
Schneider Electric
AP9614 Relay I/O Card 3


Universal I/O
1
2
USB
Schneider Electric
AP9614 Relay I/O Card 3
Status
RESET
OK
STARTING
COM ERROR
FAULT