

HP ProStudio 4 All-in-One G1i 23.8 inch Desktop AI PC Wolf Pro Security Edition (C72S1UT)



Collaborative power — packed in a space-saving AiO AI PC

The HP ProStudio 4 AiO G1i Desktop AI PC empowers users with business-grade features that enhance collaboration and productivity, supporting seamless coordination. Easy plug and play set up with a small footprint allows workspace organization, while the Intel® CPU[2] with a 13 TOPS NPU[3] and a 5 MP camera help users stay connected and achieve goals.



Enhanced meeting experience

Bring exceptional definition to virtual collaboration in varied settings with the 5 MP camera.[4]

Abundant ports for flexibility

With multiple ports, connect to varied accessories and ensure your AiO is enabled for productivity.[5,6]

Unified features boost output

Complete routine tasks, leaving time for all that fuels your enthusiasm with an Intel® CPU[2] and 13 TOPS NPU.[3]

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [1]

Intel® multi-core processor

Configure your HP ProStudio 4 AiO for the perfect combination of power, performance, and value. Get an Intel® Core™ Ultra CPU to handle work tasks smoothly and reliably, featuring 13 TOPS NPU for enhanced video conferencing and more. [7]

Collaboration through the NPU

Look your best on video calls and save some power too. Manage your video controls for internal and external cameras with Poly Camera Pro. Now Auto Frame, Spotlight, Background Blur, and virtual backgrounds save power running on the NPU. [8]

Protected by HP Wolf Security

HP Wolf Security for Business creates a hardware-enforced, always-on, resilient defense. From the BIOS to the browser, above, in, and below the OS, these constantly evolving solutions help protect your PC from modern threats. [10]

Hassle-free connectivity

Get a premium connectivity experience, even in dense wireless environments, with a fast and reliable gigabit-speed Wi-Fi 6E connection and Bluetooth® combo. [11]

Specifications

Form factor	All-in-One
Operating system	Windows 11 Pro ^[1]
Processor family	Intel® Core™ Ultra 7 processor
Processor	Intel® Core™ Ultra 7 265 (up to 5.3 GHz with Intel® Turbo Boost Technology, 30 MB L3 cache, 20 cores, 20 threads) [6,7]
Processor technology	Intel® vPro® Technology
Chipset	Intel® Q870 (vPro®) ^[7]
Memory	16 GB DDR5-5600 MT/s (1 x 16 GB)
Memory Slots	2 SODIMM (with support for RAID 1)
Internal Storage	512 GB PCIe® NVMe™ M.2 SSD
Graphics	Integrated
Graphics (integrated)	Intel® Graphics
Audio	Realtek ALC3252 codec, internal speaker, combo microphone/headphone jack; 2x2 W down-firing speakers
Dimensions (W x D x H)	53.96 x 31.94 x 5.25 cm (System dimensions may fluctuate due to configuration and manufacturing variances.)
Dimensions (W x D x H)	21.24 x 12.57 x 2.07 in (System dimensions may fluctuate due to configuration and manufacturing variances.)
Weight	6.3 kg (Exact weight depends on configuration.)
Weight	13.89 lb (Exact weight depends on configuration.)
Package dimensions (W x D x H)	75.0 x 19.5 x 48.0 cm
Package dimensions (W x D x H)	29.5 x 7.7 x 18.9 in
Package weight	14 kg (Exact weight depends on configuration.)
Package weight	30.86 lb
Keyboard	HP 125 v2 Wired Keyboard
Pointing device	HP 125 Wired Mouse
Camera	5 MP RGB fixed camera (pull-up) with integrated dual array microphones (normal SNR) ^[16]
Ports	1 USB Type-A 10Gbps signaling rate; 1 3.5 mm universal audio jack; 1 USB Type-C® 20Gbps signaling rate (15W charging) ^[11]
Expansion slots	1 M.2 2230; 2 M.2 2280 (1 M.2 2230 slot for WLAN and Bluetooth® combo and 2 M.2 2280 slots for NVMe SSD storage)
Ports	1 USB Type-A 10Gbps signaling rate; 1 HDMI-in 1.4; 1 HDMI-out 2.1; 1 RJ-45; 2 USB Type-A 5Gbps signaling rate (keyboard wake capable); 1 USB Type-C® 10Gbps signaling rate (with DisplayPort™ Alt Mode)
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card, vPro®
Power	65 W external AC power adapter
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced or recyclable; 5% REE recycled magnets in system; 20% recycled metal in enclosure; 60% recycled plastic in system; 25% ocean-bound plastic in thermal fan module; 5% ocean-bound plastic in speaker enclosure; 35% recycled indium and 20% recycled glass in display panels
Software included	HP Notifications; HP PC Hardware Diagnostics UEFI; HP PC Hardware Diagnostics Windows
UPC number	(ABA) 199642121126; (ABC) 199642120952

Top Recommended Displays, Accessories and Services

Series 5 Pro

HP Series 5 Pro 23.8 inch FHD Monitor - 524pf	9D9L6UT
---	---------

Wired Headset

Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	8X228AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[2] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[4] No camera option available and must be configured at the time of purchase.

[5] Accessories are not included and sold separately.

[6] Flex port is an optional feature that must be configured at the time of purchase. Choose from the following flex ports: 2 x USB 3.2 Gen 1, 3 x USB 3.2 Gen 2, 1x DP2.0, 1 x HDMI 1.4 (in), 1 x RJ-45.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[8] Poly software planned to be available Summer 2024. Requires Windows OS.

[10] HP Wolf Security for Business requires Windows 10 or 11 Pro and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features.

[11] Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs and available in countries where Wi-Fi 6E is supported. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 6E (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[11] Headphone/microphone combo OMTP and CTIA.

[16] Both camera options come with integrated ISP+ camera technology to support AI Human Presence Detection (Walk Away Lock and Wake On Approach) both camera options support microphones with Next Gen AI Noise Reduction and Echo Cancellation.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

