



## Drive strategy with the efficiency and power of next-gen AI

Propel your business forward with AI that uses your own data to make strategic business decisions. Discover what you can do with AI applications<sup>[4]</sup>, advanced collaboration features, and optimized battery life on the HP EliteBook X G1i Next Gen AI PC.



### HP Recommends Windows 11 Pro

Summarize and rewrite content, get relevant recommendations, and stay organized with Microsoft Copilot.<sup>[10]</sup>

### Intel® powers next-gen AI PCs

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor with an NPU.<sup>[2,3]</sup>

### Long battery life

Get more done in between charges with battery life that is efficiently managed by next-gen AI.<sup>[3]</sup>

## Featuring

### HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot.<sup>[6]</sup>

### Intel® powers next Gen AI PCs

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor purposely built for the next era of AI software. Three compute engines manage AI workloads, help improve video conferencing and allow for advanced content creation.<sup>[7]</sup>

### Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7.<sup>[8]</sup>

### Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click.<sup>[9]</sup>

### HP Sure Sense

Malware is evolving rapidly beyond traditional antivirus capabilities. Protect your PC against never-before-seen attacks with HP Sure Sense, which combines behavioral analysis with advanced AI techniques to provide exceptional protection.<sup>[12]</sup>

## Specifications

<b>Operating system</b>	Windows 11 Pro
<b>Processor family</b>	Intel® Core™ Ultra 7 processor
<b>Processor</b>	Intel® Core™ Ultra 7 256V (up to 4.8 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 8 cores, 8 threads) [6,7]
<b>Internal Storage</b>	512 GB PCIe® NVMe™ SSD
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® Arc™ Graphics
<b>Display</b>	35.6 cm (14") diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 400 nits, low power, 100% sRGB with HP Eye Ease
<b>Display</b>	14" diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 400 nits, low power, 100% sRGB with HP Eye Ease <sup>[16,17,18,19]</sup>
<b>Display size (diagonal)</b>	35.6 cm (14")
<b>Display size (diagonal)</b>	14"
<b>Audio</b>	Audio by Poly Studio, quad stereo speakers with discrete amplifiers, integrated dual array microphones
<b>Dimensions (W x D x H)</b>	31.39 x 21.99 x 1.05 cm (front); 31.39 x 21.99 x 1.49 cm (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Dimensions (W x D x H)</b>	12.36 x 8.66 x 0.41 in (front); 12.36 x 8.66 x 0.59 in (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Weight</b>	Starting at 1.18 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Weight</b>	Starting at 2.6 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Keyboard</b>	HP Premium Keyboard – spill-resistant, soft grey, backlit keyboard with DuraKeys
<b>Pointing device</b>	Clickpad with multi-touch gesture support
<b>Input devices</b>	Gyroscope; Thermal sensor; Hall effect sensor; Color sensor with Ambient light sensing; Inertial Measurement Unit sensor
<b>Ports</b>	2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1, HP Sleep and Charge); 1 USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4); 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 USB Type-A 5Gbps signaling rate (powered) <sup>[14]</sup> <i>(Cables are not included.)</i>
<b>Wireless</b>	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card
<b>Power</b>	HP 65 W USB Type-C® GaN slim power adapter <sup>[22]</sup>
<b>Battery type</b>	HP Long Life 6-cell, 68 Wh Li-ion polymer
<b>Ecolabels</b>	TCO Certified
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Sustainable impact specifications</b>	Low halogen
<b>UPC number</b>	198990731834
<b>Manufacturer Warranty</b>	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <a href="http://www.hp.com/go/cpc">http://www.hp.com/go/cpc</a> .

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.

[4] ISV solutions are sold separately and may require a subscription and NPU.

[6] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors. ISV solutions are sold separately and may require a subscription and NPU.

[8] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[9] HP Sure Click requires Windows 10 and higher. See [https://bit.ly/2PrLT6A\\_SureClick](https://bit.ly/2PrLT6A_SureClick) for complete details.

[10] Microsoft Copilot requires Windows 11. Some features require an NPU. Timing of feature delivery and availability varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[12] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

## Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[14] USB 20Gbps speed is not available with Thunderbolt™ 4.

[16] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[17] HP Sure View integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[18] Actual brightness will be lower with touchscreen or Sure View.

[19] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[22] Availability may vary by country.

---

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Ultra, Thunderbolt, Arc and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

