



Drive strategy with the efficiency and power of next-gen AI

Propel your business forward with AI that uses your own data to make strategic business decisions. Discover what you can do with AI applications^[4], advanced collaboration features, four versatile use modes, and optimized battery life on the HP EliteBook X Flip G1i Next Gen AI PC.



HP Recommends Windows 11 Pro

Summarize and rewrite content, get relevant recommendations, and stay organized with Microsoft Copilot.^[10]

Intel® powers next-gen AI PCs

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor with an NPU.^[2,3]

Long battery life

Get more done in between charges with battery life that is efficiently managed by next-gen AI.^[3]

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot.^[6]

Intel® powers next Gen AI PCs

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor purposely built for the next era of AI software. Three compute engines manage AI workloads, help improve video conferencing and allow for advanced content creation.^[7]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7.^[8]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click.^[9]

HP Sure Sense

Malware is evolving rapidly beyond traditional antivirus capabilities. Protect your PC against never-before-seen attacks with HP Sure Sense, which combines behavioral analysis with advanced AI techniques to provide exceptional protection.^[10]

Specifications

Operating system	Windows 11 Pro
Processor family	Intel® Core™ Ultra 7 processor
Processor	Intel® Core™ Ultra 7 258V (up to 4.8 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 8 cores, 8 threads) [6,7]
Memory	32 GB LPDDR5x-8533 MT/s (onboard)
Internal Storage	1 TB PCIe® NVMe™ SSD
Graphics (integrated)	Intel® Arc™ Graphics
Display	35.6 cm (14") diagonal, WUXGA (1920 x 1200), touch, IPS, BrightView, 800 nits, 100% sRGB, HP Sure View 5 integrated privacy screen
Display	14" diagonal, WUXGA (1920 x 1200), touch, IPS, BrightView, 800 nits, 100% sRGB, HP Sure View 5 integrated privacy screen ^[16,17,18,19]
Display size (diagonal)	35.6 cm (14")
Display size (diagonal)	14"
Audio	Audio by Poly Studio, quad stereo speakers with discrete amplifiers, integrated dual array microphones
Dimensions (W x D x H)	31.39 x 21.99 x 1.05 cm (front); 31.39 x 21.99 x 1.47 cm (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Dimensions (W x D x H)	12.36 x 8.66 x 0.41 in (front); 12.36 x 8.66 x 0.58 in (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Weight	Starting at 1.4 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 3.09 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	HP Premium Keyboard – spill-resistant, atmosphere blue, backlit keyboard
Pointing device	Clickpad with multi-touch gesture support
Input devices	Gyroscope; Thermal sensor; Hall effect sensor; Color sensor with Ambient light sensing; Inertial Measurement Unit sensor
Camera	5 MP IR AI camera
Ports	2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1, HP Sleep and Charge); 1 USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4); 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 USB Type-A 5Gbps signaling rate (powered) ^[14] <i>(Cables are not included.)</i>
Wireless	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card
Power	HP Smart 65 W USB Type-C™ adapter ^[22]
Battery type	HP Long Life 6-cell, 68 Wh Li-ion polymer
Ecolabels	TCO Certified
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen
UPC number	198990732374
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.

[4] ISV solutions are sold separately and may require a subscription and NPU.

[6] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors. ISV solutions are sold separately and may require a subscription and NPU.

[8] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[9] HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

[10] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[14] USB 20Gbps speed is not available with Thunderbolt™ 4.

[16] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[17] HP Sure View integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[18] Actual brightness will be lower with touchscreen or Sure View.

[19] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[22] Availability may vary by country.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Ultra, Thunderbolt, Arc and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

