

HPE ProLiant DL320 Gen11

HPE ProLiant DL320 Gen11 3508U 2.1GHz 8c 1P 1x16GB-R 8SFF MR408i-o 2x480GB SSD 2x800W PS AP Server (P85585-375)

What's new

- Powered by the 4th and 5th Gen Intel® Xeon® Scalable Processors with next-generation 5nm technology that supports up to 60 cores at 270W and 16 DIMMs of DDR5 memory up to 5600 MT/s.
- 16 DIMMs per processor for up to 2 TB total DDR5 memory with increased memory bandwidth and performance, and lower power requirements.
- Advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 2x16 PCIe Gen5 and 1 OCP 3.0 slots.
- Includes the new HPE Integrated Lights-Out 6 (iLO 6) server management software that enables you to securely configure, monitor, and update your HPE ProLiant Gen11 servers seamlessly, from anywhere.
- Supports hot-pluggable or internal, high-availability RAID1 NVMe M.2 boot options.
- Support for up to four single-wide or two double-wide GPUs in the front cage with the GPU CTO server.

Overview

Are you looking to run edge AI workloads like Computer Vision that need GPU accelerators or distributed data solutions that require expandable storage?

The HPE ProLiant DL320 Gen11 is a 1U 1P server with a unique compact design and workload-driven modular design that is purpose-built for edge computing delivering exceptional performance at 1P economics and an excellent choice for both virtualized and containerized workloads.

Powered by 4th and 5th Gen Intel® Xeon® Scalable Processors with up to 60 cores, 270W, increased memory capability (up to 2 TB 5600 MT/s), and high-speed PCIe Gen5 supporting up to four single-wide GPUs (or two double-wide), the HPE ProLiant DL320 Gen11 server is a perfect low-cost, 1U 1P, performance solution.

The HPE ProLiant Gen11 servers are engineered to optimize IT at the edge with a cloud operating experience, built-in security, and optimized performance for workloads to drive your business forward.

Features

Intuitive Cloud Operating Experience: Simple, Self-service, and Automated

HPE ProLiant DL320 Gen11 servers are engineered for your hybrid world. The HPE ProLiant DL320 Gen11 servers simplify the way you control your business's compute—from edge to cloud—with a cloud operating experience.

Transform business operations and pivot your team from reactive to proactive with global visibility and insight through a self-service console.

Automate tasks for efficiency in deployment, instant scalability, and seamless, simplified support and lifecycle management reducing tasks and shortening maintenance windows.

These experiences are engineered and built into all HPE ProLiant Gen11 servers, whether purchased as physical servers or consume as-a-service using HPE GreenLake as your compute and storage demands grow.

Simplify and secure server management from edge to cloud with HPE Compute Ops Management. HPE Compute Ops Management is an as-a-service compute management experience that delivers greater simplicity, agility, and speed across your entire compute landscape, globally.

Trusted Security by Design: Uncompromising, Fundamental, and Protected

The HPE ProLiant DL320 Gen11 server is tied into the silicon root of trust and the 4th and 5th Gen Intel® Xeon® Scalable Processor, a dedicated security processor embedded in the Intel Xeon system on a chip (SoC), to manage secure boot, memory encryption, and secure virtualization.

HPE ProLiant Gen11 servers use the silicon root of trust to anchor the firmware of an HPE ASIC, creating an immutable fingerprint for the Intel® Xeon® Processor that must be matched exactly before the server will boot. This ensures malicious code is contained and healthy servers are protected.

HPE ProLiant Gen11 servers continuously protect healthy servers by providing rapid detection of security-compromised servers, even to the point of not allowing them to boot if it identifies and contains malicious code, and secure servers at the edge with IDevID certificates installed by default.

HPE ProLiant Gen11 servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of the operating system, application, and data connections, providing the fastest path to bring a server back online and into normal operations.

From silicon to software, from factory to cloud, and from generation to generation, HPE ProLiant Gen11 is engineered with a fundamental security approach to defend against increasingly complex threats through an uncompromising commitment to constant security advancements that are built into our DNA.

Optimized Performance for your Workloads: Accelerated, Open, and Efficient

The HPE ProLiant DL320 Gen11 server is an excellent choice for virtualized workloads such as software-defined compute, CDN, and VDI, and secure edge apps that require balancing processor, memory, and network bandwidth.

Harness major computer performance. The HPE ProLiant DL320 Gen11 server is powered by 4th and 5th Gen Intel® Xeon® Scalable Processors with modern 5nm technology that support up to 60 cores and 270W TDP.

Enjoy advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 2x16 PCIe Gen5 and 1 OCP slots to improve I/O throughput and reduce latency.

Utilize 16 DIMM channels per processor for up to 2 TB total DDR5 memory with increased memory bandwidth and performance, and lower power requirements.

Benefit from real-time operational feedback on server performance plus recommendations for fine-tuning BIOS settings to customize for changing business needs.

Delivered As-a-Service

The HPE ProLiant DL320 Gen11 server is supported by HPE GreenLake to simplify IT. With 24x7 monitoring and management, our experts do the heavy lifting to manage your environment with services built into consumption-based solutions.

Hewlett Packard Enterprise provides customers choice in how they acquire and consume IT. Beyond traditional financing and leasing, HPE offers options that free trapped capital, accelerate infrastructure updates and provide for on-premises pay-per-use consumption with HPE GreenLake.

Rapidly deploy a broad portfolio of cloud services such as, containers, compute, virtual machines (VMs), accelerated storage, data protection, and more. Workload-optimized, preconfigured solutions can be quickly on-boarded, accelerating your agility

Benefit from real-time operational feedback on server performance plus recommendations for fine-tuning BIOS settings to customize for changing business needs.

Technical specifications	HPE ProLiant DL320 Gen11 3508U 2.1GHz 8c 1P 1x16GB-R 8SFF MR408i-o 2x480GB SSD 2x800W PS AP Server
Product Number	P85585-375
Processor core available	8 core
Processor cache	22.5 MB L3
Processor name	Intel® Xeon® Bronze 3508U (8 core, 2.10 GHz, 22.5 MB L3, 125W)
Processor number	1 processor included
Processor speed	2.10 GHz
Memory type	HPE DDR5 Smart Memory
Included drives	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
Optical drive type	None included, optional HPE 9.5mm SATA DVD-RW Optical Drive or HPE Mobile USB DVD-RW Drive.
Security	UEFI Secure Boot and Secure Start support. Intel® Software Guard Extensions (SGX) support. Immutable Silicon Root of Trust. Optional Trusted Supply Chain, iLO Security modes, TPM, Chassis Intrusion detection and Bezel Locking kits.
Infrastructure management	Included - HPE Compute Ops Management, HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download). Optional - HPE iLO Advanced, and HPE OneView Advanced.
Power supply type	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
Expansion slots	Maximum, 2 PCIe Gen5 & 1 OCP 3.0 PCIe Gen5, for detail descriptions please refer to the QuickSpecs.
Network controller	Broadcom BCM5720 Ethernet 1Gb 2-port BASE-T Adapter
Storage controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
System fan features	7x Standard Fans
Form factor	1U Rack
Warranty	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of on-site support coverage. Additional information regarding worldwide limited warranty and technical support is available at: https://support.hpe.com/hpesc/public/docDisplay?docId=sd00004309en_us . Additional HPE support and service coverage, to supplement the product warranty, is available. For more information, visit: https://www.hpe.com/support .
Product dimensions	60 x 91.6 x 24.1 cm
Weight	25.8 kg

Technical specifications

HPE ProLiant DL320 Gen11 3508U 2.1GHz 8c 1P 1x16GB-R 8SFF MR408i-o 2x480GB SSD 2x800W PS AP Server

Accelerators

Supports up to two double-wide or four single-wide PCIe Accelerators (GPU), depending on model. See QuickSpecs for details.

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Advisory & Professional services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Support services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.
- **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

[For additional technical information, available models and options, please reference the QuickSpecs](#)

Visit [HPE.com](https://www.hpe.com)

[Chat now](#)

© Copyright 2025 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel, Intel Xeon, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product.

[PSN1014909342WWEN](#), November, 2025.

HEWLETT PACKARD ENTERPRISE

[hpe.com](https://www.hpe.com)

