


Lenovo ThinkVision T27-40 Monitor

Adds intelligence to your workflow.




Enables greater power savings

Match your screen to your workflow with the ThinkVision T27-40 Monitor's 48Hz - 120Hz variable refresh rate¹, optimized for seamless visuals while saving energy.



Delivers clear visuals and ample connectivity

Enjoy clear, distortion-free visuals with the T27-40 Monitor's 27-inch In-Plane Switching panel technology delivers premium, vibrant colors from any viewing angle. Get more connected and compatible with a wide range of devices using the USB hub, unlocking greater productivity for your workflows.



Makes fleet management easy and intuitive

Manage and control your monitor assets with Lenovo Display Fleet Manager (LDFM). This innovative software solution empowers IT managers with robust tools for streamlined asset management, efficient firmware upgrades, and centralized settings control.

Lenovo ThinkVision T27-40 Monitor

Display

Panel Size
27-inch

Screen Dimensions
607.1 mm x 350.6 mm

Panel Type
4-sided Ultra Thin,
In-Plane Switching

Active Area
597.9 mm x 336.3 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.3114 mm x 0.3114 mm

**Dot/Pixel Per Inch
(DPI/PPI)**
82

**Viewing Angle
(H x V @ CR 10:1)**
178° / 178°

Response Time (G to G)
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
48Hz - 120Hz

Brightness
300 cd/m²

Contrast Ratio (Typical)
1500:1

**Dynamic Contrast Ratio
(Typical)**
3M:1

**Color Gamut
(Coverage Ratio)**
99% sRGB (CIE 1931),
99% BT.709 (CIE 1931)

Color Support (Typical)
16.7 Million

Color Depth
8-bit (6+FRC)

Anti-glare
Yes

Connectivity

Video Signal
1 x HDMI 1.4²
1 x DP 1.2
1 x VGA

USB Upstream
1 x USB-B (USB 5Gbps / USB 3.2 Gen 1)³

USB Downstream
3 x USB-A (USB 5Gbps / USB 3.2 Gen 1,
1 x BC1.2)³
1 x USB-C⁴ (USB 5Gbps / USB 3.2 Gen 1,
Up to 15W PD (data only))³

Multimedia

Modular Camera/Speaker Support
Yes (Optional Support⁵)

Special Features

Software
LDFM (Lenovo Display Fleet Manager)
Lenovo ThinkColour (Lenovo Accessories
and Display Manager)⁶

Natural Low Blue Light
Yes

Power

Power Consumption (Typ. / Max.)
15.0W / 75.0W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-Off Mode
< 0.3W

**ENERGY STAR Power Consumption
(Pon/E_{REC})**
12.5W / 39.5kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 23.5°

Swivel Angle (Left / Right)
-45° / 45°

Lift (Max. Range)
155 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support
Yes, by ThinkCentre Tiny
Mounting Kit⁷ (PN: 4XFIR07369)

Kensington Nano Security Slot
Yes (2.5 mm x 6 mm)

Cable Management
Yes

Bezel Color
Eclipse Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top)
2.0 mm

Bezel Width (Bottom)
10.4 mm

Dimension & Weight

**Size Packed
(W x D x H, mm/inch)**
693.0 x 150.0 x 420.0 mm
27.28 x 5.91 x 16.54 inches

**Size Unpacked w/ Stand
(Highest Position)
(W x D x H, mm/inch)**
611.9 x 195.0 x 537.8 mm
24.09 x 7.68 x 21.17 inches

**Size Unpacked w/ Stand
(Lowest Position)
(W x D x H, mm/inch)**
611.9 x 195.0 x 382.8 mm
24.09 x 7.68 x 15.07 inches

**Size Unpacked w/o Stand
(Head Only)
(W x D x H, mm/inch)**
611.9 x 46.0 x 355.2 mm
24.09 x 1.81 x 13.98 inches

Weight Packed (kg / lbs.)
9.1 kg / 20.1 lbs.

Weight Unpacked (kg / lbs.)
6.5 kg / 14.3 lbs.

Weight (Head Only) (kg / lbs.)
4.4 kg / 9.7 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

DP Cable (Cable Length)
1 x DP 1.2 Cable (1.8 m)

USB Cable (Cable Length)
1 x USB Type-B to Type-A Gen 1 Cable
(1.8 m)

Quick Setup Guide
Yes

Certification

ENERGY STAR Certification
Yes

TCO
10

TCO Edge
2.1

EPEAT
Gold

Windows Certification
Windows 10, Windows 11

EU Energy Level Certification
Yes (Level-D)

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
5 Stars

**TÜV Rheinland Low Blue Light
(Hardware Solution)**
Yes

Eyesafe Display Certification
Yes (Eyesafe 2.0)



¹ VRR as specified in HDMI 2.1, DRR for Microsoft Windows. | ² Supports 1920 x 1080 @ 120Hz as specified in HDMI 1.4. | ³ The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed. USB 2.0: 480 Mbit/s; USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1) 5 Gbit/s; USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2) 10 Gbit/s; USB4⁴ 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps) 20 Gbit/s; USB4⁴ 40Gbps (USB 40Gbps) 40 Gbit/s; Thunderbolt™ 3/4: 40 Gbit/s. | ⁴ USB Type-C and USB-C are registered trademarks of USB Implementers Forum. | ⁵ Compatible with ThinkVision VoIP Stack MC60 Monitor Webcam and MS30 Monitor Soundbar. | ⁶ Formerly Lenovo Display Control Center. Supports Windows 10 & 11, Mac OS (functions vary across systems). | ⁷ Sold separately. Need to assemble ThinkCentre Tiny mounting kit (PN: 4XFIR07369) to support Tiny PC installation.

© 2025 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others. Specifications may vary depending upon region.