

# HPE ProLiant DL360 Gen11

HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 1P 2x32GB-R 8SFF NS204i-u MR408i-o 2x800W PS AP Server (P81578-375)



## What's new

- Powered by 5th Gen Intel® Xeon® Scalable processors that supports up to 64 cores & 385W, and 16 DIMMs for up to 8 TB of high bandwidth DDR5 memory up to 5600 MHz.
- 16 DIMMs per processor for up to 8 TB total DDR5 memory per server with increased performance, High Bandwidth Memory (HBM) support, and lower power requirements.
- Advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 2 x16 PCIe Gen5 and 2 OCP slots.
- Includes the new HPE Integrated Lights-Out 6 (iLO 6) server management software that enables you to securely configure, monitor, and update your HPE ProLiant Gen11 servers seamlessly, from anywhere.
- Supports up to 3 single wide (SW) GPUs[1] to accelerate graphic intense workloads.

## Overview

Are you looking for a scalable, compute-dense solution for hybrid cloud or other data workloads in a virtualized and containerized environment?

The HPE ProLiant DL360 Gen11 server is a rack-optimized, 1U 2P solution that delivers exceptional compute performance, upgraded high-speed data transfer rate, and memory depth at 2P compute capability.

Powered by 4th and 5th Gen Intel® Xeon® Scalable Processors with up to 64 cores, 8TB of memory, and 20 EDSFF drives as well as increased memory bandwidth and high-speed PCIe Gen5 I/O, the HPE ProLiant DL360 Gen11 server is a perfect solution for Electronic Design Automation (EDA), CAD, and VDI.

The HPE ProLiant 360 Gen11 server is engineered to optimize IT with a cloud operating experience, built-in security, and optimized performance for workloads to drive your business forward.

- Supports Liquid Cooling Modules for highest thermal design points (TDPs).

## Features

### **Intuitive Cloud Operating Experience: Simple, Self-service, and Automated**

HPE ProLiant DL360 Gen11 servers are engineered for your hybrid world. ProLiant DL360 Gen11 servers are powered by 4th and 5th Gen Intel® Xeon® processors and simplify the way you control your business's compute—from edge to cloud—with a cloud operating experience.

Transform business operations and pivot your team from reactive to proactive with global visibility and insight through a self-service console.

Automate tasks for efficiency in deployment, instant scalability, and seamless, simplified support and lifecycle management to reduce and shorten maintenance windows.

Self-service automated experiences are engineered and built into all HPE ProLiant Gen11 servers, whether purchased as physical servers or consumed as-a-service using HPE GreenLake as your compute and storage demands grow.

Simplify and secure server management from edge to cloud with HPE Compute Ops Management. HPE Compute Ops Management is an as-a-service compute management experience that delivers greater simplicity, agility, and speed across your entire compute landscape, globally.

### **Trusted Security by Design: Uncompromising, Fundamental, and Protected**

The HPE ProLiant DL360 Gen11 server utilizes the HPE Silicon Root of Trust, HPE's fundamental approach to security that provides zero-trust architecture at the silicon level and ensures all server essential firmware is free from malware or compromised code.

Powered by 4th and 5th Gen Intel® Xeon® Scalable Processors, adds hardware- and software-assisted security features, including Intel® Software Guard Extensions and Intel® Boot Guard, which help secure the server hardware foundation on which critical apps run and better protect data in memory.

HPE ProLiant Gen11 servers continuously protect healthy servers by a) providing rapid detection of security-compromised servers, even to the point of not allowing them to boot if it identifies malicious code, and b) securing servers at the edge with IDevID certificates installed by default.

HPE ProLiant Gen11 servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of the operating system, application, and data connections, providing a fast path to bring a server back online and into normal operations.

Embedded in Hewlett Packard Enterprise servers, HPE Integrated Lights-Out 6 (iLO 6) is an exclusive core intelligence that monitors server status, providing the means for reporting, ongoing management, service alerting, and local or remote management to quickly identify and resolve issues.

### **Optimized Performance for your Workloads: Accelerated, Open, and Efficient**

The HPE ProLiant DL360 Gen11 server is an excellent choice for EDA, CAD, CDN, general-purpose virtualization workloads (including large-scale VDI), Intelligent Video Analytics, and Platforms (VCF & Containers) that require increased compute density with built-in security and flexibility.

Harness major computer performance. The HPE ProLiant DL360 Gen11 server is powered by the 4th and 5th Gen Intel® Xeon® Scalable Processors with next-generation technology that supports up to 64 cores, 385W, and up to 8 TB of memory.

The HPE ProLiant DL360 Gen11 server provides advanced data transfer rates and higher network speeds from the PCIe Gen5 serial expansion bus, with up to 3 x16 PCIe Gen5 and 2 OCP slots to improve I/O throughput and reduce latency.

The server provides 16 DIMMs per processor for up to 8 TB total DDR5 memory with increased memory bandwidth and performance, and lower power requirements.

The HPE ProLiant DL360 Gen11 server provides real-time operational feedback

on server performance plus recommendations for fine-tuning BIOS settings to customize for changing business needs.



## Technical specifications

## HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 1P 2x32GB-R 8SFF NS204i-u MR408i-o 2x800W PS AP Server


<b>Product Number</b>	P81578-375
<b>Processor core available</b>	12 core
<b>Processor cache</b>	30 MB L3
<b>Processor name</b>	Intel® Xeon® Silver 4510 (12 core, 2.40 GHz, 30 MB L3, 150W)
<b>Processor number</b>	1 processor included
<b>Processor speed</b>	2.40 GHz
<b>Memory type</b>	HPE DDR5 Smart Memory
<b>Included drives</b>	None ship standard, 8 SFF supported
<b>Optical drive type</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.
<b>Security</b>	UEFI Secure Boot and Secure Start support. Intel® Software Guard Extensions (SGX) support. Immutable Silicon Root of Trust. Optional Trusted Supply Chain, iLO Security modes, TPM, Chassis Intrusion detection and Bezel Locking kits.
<b>Infrastructure management</b>	Included - HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download). Optional - HPE iLO Advanced, and HPE OneView Advanced.
<b>Power supply type</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Expansion slots</b>	Maximum 3 PCIe Gen5 slots and maximum 2 OCP 3.0 PCIe5 slots, for detail descriptions please see QuickSpecs.
<b>Network controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE
<b>Storage controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
<b>System fan features</b>	7x High Performance Fans
<b>Form factor</b>	1U Rack
<b>Warranty</b>	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: <a href="https://h20564.www2.hp.com/hpsc/wc/public/home">https://h20564.www2.hp.com/hpsc/wc/public/home</a> . Additional HPE support and service coverage, to supplement the product warranty, is available. For more information, visit <a href="https://www.hp.com/support">https://www.hp.com/support</a>
<b>Product dimensions</b>	60 x 99 x 24.1 cm
<b>Weight</b>	31.38 kg



[For additional technical information, available models and options, please reference the QuickSpecs](#)

**Make the right purchase decision.  
Contact our presales specialists.**

[Find a partner](#)



**Share now**



**Get updates**

## HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

### **Advisory & Professional services**

Experts can help you map out your path to hybrid cloud and optimize your operations.

### **Managed services**

HPE runs your IT operations, giving you unified control, so you can focus on innovation.

### **Support services**

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.
- **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

### **Lifecycle Services**

Address your specific IT deployment project needs with tailored project management and deployment services.

### **HPE Education Services**

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

**Defective Media Retention** is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

## HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

Visit [HPE.com](https://www.hpe.com)



© Copyright 2025 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel, Intel Xeon, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product  
[PSN1014888020WWEN](#), March, 2025.