

ThinkStation P3 Tiny Gen 2

Whether managing projects, developing software, or creating high-end content, this workstation, powered up to one 65W Intel® Core™ Ultra (Series 2) processor, delivers powerful performance tailored for business professionals who demand speed, responsiveness, and efficiency. The discrete GPU options, including the NVIDIA® RTX A1000 or RTX A400, ensure exceptional graphics capabilities for intensive design, rendering, and analytical tasks, while integrated Intel® Graphics offer reliable performance for everyday business applications. Supporting up to 128GB DDR5-6500 memory, this system enables seamless multitasking and ultra-fast data processing, making it ideal for professionals working with large datasets, complex simulations, or creative workflows.



**Elevate Professional Endeavors
with Powerhouse Workstations**

The support for up to four independent displays through onboard DisplayPort, HDMI punch out port 1 (VGA / HDMI® / DP / USB-C®), and punch out port 2 (VGA / HDMI® / DP / Thunderbolt™ 4) allows users to create a highly customized and expansive visual workspace. Whether managing complex data sets, multitasking across various software tools, or presenting content seamlessly, this multi-display support significantly enhances productivity and workflow efficiency.

The robust security features, including a discrete TPM 2.0 chipset provide hardware-based encryption for sensitive data, secure credential storage, and ensures system integrity by preventing unauthorized access at the hardware level. Additionally, 3 x 7 mm Kensington® Security Slot™ offers flexible anchoring options to secure the workstation to a desk or fixed location, effectively deterring theft.

The compact dimensions of 179 x 182.9 x 37mm and weight of 1.4kg (3 lbs) make this 1L Tiny workstation an ideal solution for modern business professionals seeking efficiency without compromising performance. Its ultra-small footprint allows it to fit seamlessly into any workspace, freeing up valuable desk space for greater productivity and organization.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- On-site support if needed
- Normally next business day service
- Agreed appointment times

Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

Lenovo Essential FHD Webcam Gen 2

- Built-in microphones and camera cover
- Smart control with broad compatibility
- Flexible mounting with fast USB setup



PN: 4XC1S15018

ThinkStation P3 Tiny Gen 2

Performance

Processor

Up to one 65W Intel Core Ultra (Series 2) processor

Operating System*

Windows 11 Pro
 Windows 11 Home
 Windows 11 Home Single Language
 Ubuntu Linux LTS
 Red Hat Enterprise Linux (certified only)

Graphics

Intel Graphics (integrated)
 NVIDIA A400
 NVIDIA A1000 8GB

Chipset

Intel Q870 chipset

Memory¹

Up to 128GB (2x 64GB DDR5 CSODIMM)

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage²

Up to 3x M.2 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Design

Dimensions³

179 x 182.9 x 37mm (7.05 x 7.2 x 1.5 inches, with rubber feet)

³The system dimensions may vary depending on configurations.

Weight⁴

1.4 kg (3 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

One onboard Gigabit Ethernet
 Additional Ethernet options via PCIe adapter

WLAN + Bluetooth⁵

Intel Wi-Fi 7 BE200, 802.11be 2x2 Wi-Fi + Bluetooth 5.4

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Security

Discrete TPM 2.0
 Kensington Security Slot, 3 x 7 mm
 Chassis intrusion switch

Manageability

System Management⁶

Intel vPro Enterprise with Intel AMT16.0*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications^{7 8}

ENERGY STAR 9.0
 EPEAT Gold Registered
 RoHS compliant
 TCO Certified 10.0

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

Other Certifications

MIL-STD-810H military test passed