



Flip flexibility meets AI performance, ready for any task

Empower high-performing teams with an AI-enhanced PC that offers the power, security, and collaboration tools essential for both office and hybrid work environments. The HP EliteBook 8 Flip G1i 13 inch Notebook AI PC features four modes for work, note-taking, sharing content and consuming content meeting the requirements of multitasking teams worldwide.



HP Recommends Windows 11 Pro

Summarize and get relevant content recommendations with Microsoft Copilot.[8]

Intel® powers PCs enhanced by AI

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor with an 11 TOPS NPU.[2,3]

Long battery life

Get more done in between charges with battery life that is enhanced by AI.[3]

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [5]

Powerful Intel® processor

Help speed up demanding business applications with the latest generation Intel® Core™ processor. [2]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7. [6]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [7]

Collaboration through the NPU

Look your best on video calls and save some power too. Manage your video controls for internal and external cameras with Poly Camera Pro. Now Auto Framing, Spotlight, Background Blur, and virtual backgrounds save power running on the NPU. [9]

Specifications

Operating system	Windows 11 Pro
Processor family	Intel® Core™ Ultra 7 processor
Processor	Intel® Core™ Ultra 7 255U (up to 5.2 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 12 cores, 14 threads) [6,7]
Internal Storage	512 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® Graphics
Display	33.8 cm (13.3") diagonal, WUXGA (1920 x 1200), touch, IPS, BrightView, Corning® Gorilla® Glass 7, 800 nits, 100% sRGB, HP Sure View 5 integrated privacy screen
Display	13.3" diagonal, WUXGA (1920 x 1200), touch, IPS, BrightView, Corning® Gorilla® Glass 7, 800 nits, 100% sRGB, HP Sure View 5 integrated privacy screen ^[14,15,16,17]
Display size (diagonal)	33.8 cm (13.3")
Display size (diagonal)	13.3"
Audio	Audio by Poly Studio, dual stereo speakers with discrete amplifiers, integrated dual array microphones
Weight	Starting at 1.39 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 3.08 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	HP Premium Keyboard – spill resistant, backlit keyboard
Pointing device	Clickpad with multi-touch gesture support
Input devices	Accelerometer; Gyroscope; Magnetometer; Thermal sensor; HP Tamper Lock; Hall effect sensor; Color sensor with Ambient light sensing
Ports	2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1, HP Sleep and Charge); 1 USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4, HP Sleep and Charge); 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 USB Type-A 5Gbps signaling rate (powered) ^[12] <i>(HDMI cable sold separately.)</i>
Ports	1 smart card reader
Wireless	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card, non-vPro®
Power	65 W USB Type-C™ adapter ^[20]
Battery type	HP Long Life 3-cell, 62 Wh Li-ion polymer
Ecolabels	TCO Certified
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen; 40% post-consumer recycled plastic; Bulk packaging available; 50% ocean-bound plastic; 80% recycled metal; 100% of HP paper-based packaging is from recycled or certified sustainable sources
UPC number	199251445958
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. HP Worldwide Limited Warranty for the battery is aligned with the warranty period of the HP Hardware Product. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

Topload Bags

HP Travel Plus 15L 14-inch Laptop Bag	A2CE2AA
---------------------------------------	---------

Sleeves

HP Renew Executive 14-inch Laptop Sleeve	6B8Y3AA
--	---------

Backpacks

HP Renew Executive 16 Laptop Backpack	6B8Y1UT
---------------------------------------	---------

Wireless Keyboards

HP 685 Comfort Dual-Mode Keyboard	8T6L9UT
HP 725 Multi-Device Rechargeable Wireless Keyboard	9T5B2AA

Wireless Mice

HP 515 Ultra-Fast Rechargeable Wireless Mouse	9C2F7AA
HP 685 Comfort Dual-Mode Mouse	8T6M0UT
HP 715 Rechargeable Multi-Device Mouse	6E6F0AA

Port Replicators

HP Universal USB-C Multiport Hub	50H55UT
HP USB-C Travel Hub G3	86S97UT

Power Adapters

HP 110W USB-C Laptop Charger	8B3Y2UT
HP USB-C 65W Laptop Charger	671R3UT
HP 65W GaN USB-C Laptop Charger	600Q8UT

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.

[5] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[6] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[7] HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

[8] May require Windows Update or app download from the Microsoft Store. Microsoft Copilot is NOT available in China, Russia, Belarus, and embargoed regions Cuba, Iran, North Korea, Crimea.

[9] Poly software planned to be available Summer 2024. Requires Windows OS.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[12] USB 20Gbps speed is not available with Thunderbolt™ 4.

[14] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[15] HP Sure View Reflect integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[16] Actual brightness will be lower with touchscreen or Sure View.

[17] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[20] Availability may vary by country.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Thunderbolt and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

