



AI-ready for enterprise productivity

AI-based experiences and modern connectivity enhance user productivity. The HP EliteBook 6 G1i AI 16 inch PC offers an 11 TOPS NPU[3], enterprise-grade security and manageability in a highly configurable PC that meets the demanding needs of enterprise users.



HP Recommends Windows 11 Pro

Summarize and rewrite content, get relevant recommendations, and stay organized with Microsoft Copilot.[1,9]

Commanding AMD processor

Develop innovative ideas with the fast and efficient AMD Ryzen™ processor with an up to 16 TOPS NPU.[2,3]

Easy battery management

Manage battery performance and customize charging options with the easy-to-use HP Power Manager dashboard.[5]

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [6]

Powerful Intel® processor

Help speed up demanding business applications with the latest generation Intel® Core™ processor. [7]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7. [8]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [10]

Collaboration through the NPU

Look your best on video calls and save some power too. Manage your video controls for internal and external cameras with Poly Camera Pro. Now Auto Framing, Spotlight, Background Blur, and virtual backgrounds save power running on the NPU. [11]

Specifications

Operating system	Windows 11 Pro ^[1]
Product color	Pike silver aluminum
Processor family	Intel® Core™ Ultra 5 processor
Processor	Intel® Core™ Ultra 5 225U (up to 4.8 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 12 cores, 14 threads) [6,7]
Memory	16 GB DDR5-5600 MT/s (2 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	512 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® Graphics
Display	40.6 cm (16") diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 300 nits, 62.5% sRGB
Display	16" diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 300 nits, 62.5% sRGB ^[16,18,19,20]
Display size (diagonal)	40.6 cm (16")
Display size (diagonal)	16"
Audio	Audio by Poly Studio, dual stereo speakers, dual array microphones
Dimensions (W x D x H)	35.94 x 25.1 x 1.7 cm (rear); 35.94 x 25.1 x 1.09 cm (front) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Dimensions (W x D x H)	14.15 x 9.88 x 0.43 in (front); 14.15 x 9.88 x 0.67 in (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Weight	Starting at 1.75 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 3.86 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	Spill-resistant, backlit keyboard with numeric keypad
Pointing device	Clickpad with multi-touch gesture support
Input devices	HP Sure Platform; Thermal sensor; HP Tamper Lock; Hall effect sensor ^[16]
Camera	1080p FHD camera
Ports	2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1, HP Sleep and Charge); 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45; 1 security lock slot; 2 USB Type-A 5Gbps signaling rate (powered) <i>(Cables are not included.)</i>
Wireless	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card, non-vPro®
Power	65 W USB Type-C™ adapter ^[48]
Battery type	HP Long Life 3-cell, 56 Wh Li-ion polymer
Ecolabels	TCO Certified
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen; Bulk packaging available; 25% post-consumer recycled plastic; 50% recycled metal; 50% ocean-bound plastic in fan enclosure; 100% of HP paper-based packaging is from recycled or certified sustainable sources
UPC number	199251445842
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

Backpacks

HP Everyday 16-inch Laptop Backpack	A08KLUT
HP Travel Plus 30L 17-inch Laptop Backpack	A2CE0AA

Topload Bags

HP Travel Plus 22L 16-inch Laptop Bag	A2CE1AA
---------------------------------------	---------

Wireless Keyboards

HP 455 Programmable Wireless Keyboard	4R177AA
HP 685 Comfort Dual-Mode Keyboard	8T6L9UT

Wireless Mice

HP 435 Multi-Device Wireless Mouse	3B4Q5UT
HP 515 Ultra-Fast Rechargeable Wireless Mouse	9C2F7AA
HP 685 Comfort Dual-Mode Mouse	8T6M0UT

Port Replicators

HP Universal USB-C Multiport Hub	50H55UT
HP USB-C Travel Hub G3	86S97UT

Power Adapters

HP 65W GaN LC USB-C Laptop Charger	9Y3X5UT
HP 65W GaN USB-C Laptop Charger	600Q8UT
HP USB-C 65W Laptop Charger	671R3UT

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of clock speed.

[3] Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.

[5] Requires HP app and Windows OS.

[6] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[8] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[9] May require Windows Update or app download from the Microsoft Store. Microsoft Copilot is NOT available in China, Russia, Belarus, and embargoed regions Cuba, Iran, North Korea, Crimea.

[10] HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

[11] Poly software planned to be available Summer 2024. Requires Windows OS.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[16] Sold separately or as an optional feature that must be configured at purchase.

[18] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[19] HP Sure View integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[20] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. Actual brightness will be lower with touchscreen or Sure View.

[48] Availability may vary by country.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Arc, Thunderbolt and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

