

HP Z2 Tower G1i Workstation Desktop PC (CU6V2PT)



Mainstream workstation performance—reimagined

Experience new levels of performance for professional workflows. The HP Z2 Tower AI workstation is reengineered to support high-end graphics and seamlessly run both single and multi-threaded apps for fast modeling, simulation, and rendering. Enjoy easy expandability to upgrade, when needs evolve.



Reengineered performance. Refined cooling.

Unleash the power of up to 600W, triple-wide graphics and an Intel® Core™ Ultra processor[1]. Smart fan control tunes fan speeds in real-time. New lattice venting optimizes airflow intake.

Built to expand. Power to grow.

Need to upgrade graphics? Increase memory or storage?[2] Add specialized PCIe cards? With room to expand and tool-less access, you can easily upgrade and add components as needs evolve. Well suited for rack environments, now fit 1 unit in a 4U rack.[3]

Power AI-accelerated workflows

Accelerate AI inferencing and development with the Z2 Tower AI workstation. Iterate and problem solve faster on your local device with a powerful discrete GPU delivering AI TOPS while a built-in NPU[4] takes on productivity tasks.

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [7]

Smaller, Functional Design

The stunning new design features front and rear ledges, so you can easily move your system from location to location.

Independent Software Vendor Certifications

Work with confidence knowing your PC is certified by leading software vendors to ensure peak performance even on complex projects.

HP Anyware

Access the power of your Z from any device with HP Anyware—remote access software delivering fast responsiveness and image quality, even in film editing and data visualizations. [8]

Specifications

Form factor	Tower
Operating system	Windows 11 Pro ^[1]
Processor family	Intel® Core™ Ultra 9 processor
Processor	Intel® Core™ Ultra 9 285K (up to 5.7 GHz with Intel® Turbo Boost Technology, 36 MB L3 cache, 24 cores, 24 threads) [6.7]
Chipset	Intel® W880
Memory	32 GB DDR5-5600 MT/s non-ECC (2 x 16 GB)
Memory Slots	4 DRR5
Internal Storage	1 TB HP Z Turbo Drive PCIe® Gen4 TLC M.2 SSD
External drive bays	One slim ODD; One 5.25"
Graphics	Discrete
Graphics (discrete)	NVIDIA RTX™ 2000 Ada Generation (16 GB GDDR6 dedicated)
Graphics	Integrated
Graphics (integrated)	Intel® Graphics
Audio	Realtek ALC3205 codec, universal audio jack with CTIA and OMTP headset support
Dimensions (W x D x H)	17.5 x 42.6 x 38.8 cm <i>(Standard desktop orientation.)</i>
Dimensions (W x D x H)	6.9 x 16.7 x 15.2 in <i>(Standard desktop orientation.)</i>
Weight	Starting at 8.6 kg <i>(Exact weight depends on configuration.)</i>
Weight	Starting at 19 lb <i>(Exact weight depends on configuration.)</i>
Keyboard	HP 320K Wired Keyboard
Pointing device	HP Wired 320M Mouse
Ports	2 USB Type-C® 20Gbps signaling rate; 4 USB Type-A 10Gbps signaling rate; 1 headphone/microphone combo
Expansion slots	2 M.2 2280 PCIe 4 x4; 1 M.2 2230 for WLAN; 1 M.2 2280 PCIe 5 x4; 1 PCIe 4 x1 mechanical (x4 electrical); 1 PCIe 4 x4 mechanical (x16 electrical); 1 PCIe 4 x4
Ports	2 USB Type-A 10Gbps signaling rate; 2 DisplayPort™ 1.4; 1 RJ-45; 1 audio line-in/line-out; 3 USB Type-A 480Mbps signaling rate
Package dimensions (W x D x H)	59 x 49 x 29.5 cm
Package weight	Starting at 12.5 kg
Network interface	Intel® I219LM GbE
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
Power	700 W external power adapter, up to 90% efficiency, active PFC
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen; Bulk packaging available; 10% ITE-derived closed loop plastic; 25% ocean-bound plastic in system fans; Product Carbon Footprint; Contains at least 60% post-consumer recycled plastic; System has a QR code enabled experience where the user has access to a product portal – beginning December 2025, this is complete with product feature highlights, sustainability information, getting started guides, and direct setup and support options; New Energy Consumption dashboard available to customers providing timely carbon usage including recommended actions users can take to decrease carbon footprint
UPC number	199764517722

Top Recommended Displays, Accessories and Services

Series 7 Pro

HP Series 7 Pro 27 inch QHD Monitor - 727pq	8J4D8UT
---	---------

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA

Wireless Headset

Poly Voyager Focus 2 USB-C-C Headset +USB-C/A Adapter	9T9J3AA
---	---------

Messaging Footnotes

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of clock speed. Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[2] Memory and storage are optional features that must be configured at purchase.

[3] Rack mounting hardware sold separately.

[4] Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[7] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[8] Network access required. HP Anyware software and licensing are available through a 1- or 3-year subscription. Renewal is required after the subscription term. HP Anyware subscriptions are based on the number of concurrent PCoIP connections used (pay for the number of host connections, not the software) with a minimum order quantity of 5. For a limited time, an HP Anyware Professional subscription also includes access and support for ZCentral Remote Boost and ZCentral Connect and is available for purchase through an HP reseller or contact sales at hp.com/Anyware. ZCentral Remote Boost Sender requires Windows 10 and 11, RHEL/CentOS (7 or 8), or UBUNTU 18.04 or 20.04 LTS operating systems. macOS (10.14 or newer) operating system and ThinPro 7.2 are only supported on the receiver side. ZCentral Connect requires Windows (10 or 11) or Windows Server (2016 or 2019) operating system, Microsoft Active Directory and Intel Active Management Technology for select features. For system requirements and to install HP Anyware and Anyware Manager, refer to the Admin Guides at: <https://docs.teradici.com/find/product/hp-anyware>.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Pentium, the Intel logo, Intel Core, Thunderbolt, vPro, Optane, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Adobe PDF is a trademark of Adobe Systems Incorporated. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. NVIDIA, the NVIDIA logo and Quadro are trademarks and/or registered trademarks of NVIDIA Corporation in the US. and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

