

Product data sheet

Specifications



APC NetShelter Rack PDU,
Metered, 0U, 8.6kW 208V 3-phase
30A, (36) C13, (6) C19, and (2)
NEMA 5-20R outlets

AP8865US

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Metered
Cord length	5.97 ft (1.82 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide

Complementary

Input Voltage	208 V 3 phase
Height	70.5 in (1791 mm)
Width	2.2 in (56 mm)
Output Voltage	120 V 208 V
Depth	1.8 in (46 mm)
Net Weight	16.67 lb(US) (7.56 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L21-30P
Mounting Mode	Rack-mounted
Rack units	0U
USB compatible	No
Mounting position	Vertical
Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	8600 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Outlet type and quantity	2 NEMA 5-20R 36 IEC 60320 C13 6 IEC 60320 C19
--------------------------	---

Environment

Product Certifications	TAA compliance
Standards	CSA C22.2 No. 60950 UL 60950-1
Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304435327
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	78.7 in (200 cm)
Package 1 Width	4.2 in (10.7 cm)
Package 1 Length	6.4 in (16.2 cm)
Package weight(Lbs)	20.3 lb(US) (9.2 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	83 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	79 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0.1 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	53
Circularity Profile	End of Life Information
Removable battery	No
Take-back	No

Image of product / Alternate images

Alternative

