

ThinkPad T14s Gen 6 (Intel)

Designed for professionals on the move, the next-generation AI PC delivers seamless productivity with Intel® Core™ Ultra processors, enabling superior multitasking, energy efficiency, and AI-accelerated workloads. With Intel vPro®, IT teams can ensure enterprise-grade security and remote management, safeguarding data and updating devices from anywhere. Whether you're delivering client presentations, analyzing real-time market data, or collaborating across time zones, the integrated Intel® Arc™ 130V/140V/140T GPU ensures smooth performance, sharper visuals, and faster rendering. Copilot+ PC features, such as Cocreator, generate AI-powered visuals in seconds, while Live Captions break language barriers for effortless global communication. Windows Studio Effects enhances video calls with AI-driven clarity, perfect for remote negotiations or virtual boardrooms.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad T series laptops offer professional-grade durability, powerful performance with good processors, ample memory, and fast SSD storage. They feature robust security features and long battery life for productivity on-the-go.

Enhance productivity with a 14" 2.8K (2880x1800) OLED AGARAS display, delivering sharp visuals and optional multi-touch for seamless navigation. Optional 3M™ DBEF5 technology optimizes brightness efficiency, while Eyesafe® Certified 2.0 minimizes blue light exposure, ensuring comfort during extended work sessions.

The 58Wh battery delivers extended uptime for uninterrupted work, while Intel® Wi-Fi® 7 enables ultra-fast, reliable connections. Upgrade to 5G WWAN for secure, high-speed access to cloud applications and virtual meetings anywhere.

Designed for mobile business professionals, this laptop delivers the perfect balance of performance and portability. Weighing just 1.24 kg (2.72 lbs) and measuring 11.2/15.8 mm thin, it easily fits into any briefcase or carry-on.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo 15.6-inch Laptop Casual Backpack B210 Grey

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: GOA6130WUS, GOA6130WEU, GOA6130WUK

ThinkPad T14s Gen 6 (Intel)



Performance

Processor
Intel V Series Core Ultra 5 / 7 Processor (Series 2) - Lunar Lake
Intel U Series Core Ultra 5 / 7 or Intel H Series Core Ultra 7 Processor (Series 2) - Arrow Lake

AI PC Category*
AI PC (Arrow Lake)
Copilot+ PC (Lunar Lake)

Operating System*
Windows 11 Pro or Home
Ubuntu Linux

NPU*
Integrated Intel AI Boost, up to 48 TOPS

Graphics
Intel Graphics (integrated)
Intel Arc 140T GPU (integrated)
Intel Arc Graphics 130V (integrated)
Intel Arc Graphics 140V (integrated)

Memory
Arrow Lake: 16GB, 32GB or 64GB LPDDR5x-7467, soldered
Lunar Lake: 32GB LPDDR5x-8533 MoP memory, soldered

Storage¹
Up to 1x 1TB M.2 2280 PCIe NVMe SSD

¹The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

Audio*
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Dolby Voice*

Camera*
5.0MP, with privacy shutter, temporal noise reduction
5.0MP + IR discrete, with privacy shutter, Computer Vision on ISP, temporal noise reduction

Battery²
58Wh (up to 23.46 hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
65W USB-C adapter, PD 3.0
65W USB-C nano GaN adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display³
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 3M DBEF5
- 400nits, 45% NTSC, on-cell touch, Eyesafe, 3M DBEF5
- 500nits, 100% sRGB, low power, Eyesafe
- 500nits, 100% sRGB, on-cell touch, ThinkPad Privacy Guard, Eyesafe
14" 2.8K (2880x1800) OLED AGARAS 16:10
- 400nits, 100% DCI-P3, 120Hz VRR, Add-on Film touch, Dolby Vision, Eyesafe

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio
88%

Keyboard
6-row, spill-resistant, Copilot key, backlight

Touchpad
TrackPoint and glass-like Mylar surface 3-button
Trackpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions⁴
Starting at 313.6 x 219.4 x 11.2/15.8 (front/rear), 19.75 (maximum) mm
12.35 x 8.64 x 0.44/0.62 (front/rear), 0.78 (maximum) inches

⁴The system dimensions may vary depending on configurations.

Weight⁵
Arrow Lake: starting at 1.24 kg (2.72 lbs)
Lunar Lake: starting at 1.28 kg (2.82 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color
Black
Grey

Case material
Carbon fiber hybrid or aluminium (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*
Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

WWAN*
4G LTE CAT6 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Security
ThinkShield
Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello (facial recognition)*
Computer Vision-based User Presence Sensing on ISF

Manageability

System Management*⁶
Intel vPro Enterprise*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Environmental

Material
30% recycled Carbon fiber on top cover
90% recycled magnesium on keyboard frame
55% recycled aluminum on bottom cover
85% PCC recycled plastic used in backlit keycaps
90% PCC recycled plastic used in speaker enclosure
90% recycled plastic used in the 58Wh battery frame
90% PCC recycled plastic used in standard 65W slim adapter
95% PCC recycled plastic used in cable / antenna holders
100% plastic free packaging with FSC certified paper

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.