

Product data sheet

Specifications



APC Smart-UPS, Line Interactive,
2200VA, Lithium-ion, Rackmount
2U, 120V, 2x NEMA 5-20R+6x
NEMA 5-15R outlets,
SmartConnect Port+SmartSlot,
LCD [TAA]

SMTL2200RM2UCUS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V AC 1 phase
Other Input Voltages	110 V
Input Connection Type	NEMA 5-20P
Input protection type	Circuit breaker
Efficiency at full load	82...144 V
Number of input connectors	1
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Other Output Voltages	110 V
Rated power in W	1920 W
rated power in VA	1920 VA
output connection type	2 NEMA 5-20R
Crest factor	3 : 1
Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Li-Ion (Lithium Ion) internal included
Control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Alarm when on battery : distinctive low battery alarm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

UPS connectivity	Serial port USB port SmartConnect port Available expansion slot
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use
Surge energy rating	530 J
Number of rack unit	2U
Cable length	8 ft (2.4 m)
color	Black with silver front bezel
Height	3.4 in (86 mm)
Width	17.008 in (432 mm)
Depth	26.9 in (683 mm)
Net Weight	70.3 lb(US) (31.9 kg)
Mounting preference	Lower
Mounting Mode	Rack-mounted
USB compatible	Yes
Mounting mode	Rack-mounted with included kit
Provided equipment	Rack Mounting brackets
Number of power module	0
Additional specification	Cloud-enabled monitoring
Redundant	No
Range of Product	Smart-UPS
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	cULus ENERGY STAR V2.0 (USA) TAA compliance
Equipment protection policy	Lifetime : \$150000
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...25000 ft (0...7620 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dB
Online Thermal Dissipation	215 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time

[View Runtime Graph](#) 

Efficiency	View Efficiency Graph 
Battery Type	Li-Ion (Lithium Ion)
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0
Typical recharge time	2 h
RBC Quantity	1
Battery design life	8...10 year(s)
Battery Charge Power (Watts)	216 W rated
Replacement battery	APCRBC174-LI 

Ordering and shipping details

GTIN	731304740674
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	10.0 in (25.4 cm)
Package 1 Width	38.6 in (98.0 cm)
Package 1 Length	23.6 in (60.0 cm)
Package weight(Lbs)	94.05 lb(US) (42.66 kg)

Compliance

Compliance	TAA Compliant
------------	---------------

Contractual warranty

Warranty (in months)	24 Battery 36 UPS
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	578 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	570 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	7 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	2 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold



Energy efficiency

ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
--------------	----------------------------

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	58
Circularity Profile	End of Life Information
Removable battery	No
Take-back	Yes

Image of product / Alternate images

Alternative

