

ThinkPad T14s Gen 6 (Intel)

Designed for professionals on the move, the next-generation AI PC delivers seamless productivity with Intel® Core™ Ultra processors, enabling superior multitasking, energy efficiency, and AI-accelerated workloads. With Intel vPro®, IT teams can ensure enterprise-grade security and remote management, safeguarding data and updating devices from anywhere. Whether you're delivering client presentations, analyzing real-time market data, or collaborating across time zones, the integrated Intel® Arc™ 130V/140V GPU ensures smooth performance, sharper visuals, and faster rendering. Copilot+ PC features, such as Cocreator, generate AI-powered visuals in seconds, while Live Captions break language barriers for effortless global communication. Windows Studio Effects enhances video calls with AI-driven clarity, perfect for remote negotiations or virtual boardrooms.



Redefining possibilities with powerful performance and groundbreaking on-device AI


Enhance productivity with a 14" WUXGA (1920 x 1200) display, delivering sharp visuals and optional multi-touch for seamless navigation. Optional 3M™ DBEF5 technology optimizes brightness efficiency, while Eyesafe® Certified 2.0 minimizes blue light exposure, ensuring comfort during extended work sessions.

The 58Wh battery delivers extended uptime for uninterrupted work, while Intel® Wi-Fi® 7 enables ultra-fast, reliable connections. Upgrade to 5G WWAN for secure, high-speed access to cloud applications and virtual meetings anywhere.

Designed for mobile business professionals, this laptop delivers the perfect balance of performance and portability. Weighing just 1.31 kg (2.89 lbs) and measuring 16.9 mm (0.67 inches) thin, it easily fits into any briefcase or carry-on.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 15.6-inch Laptop Casual Backpack B210 Grey

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: G0A6130WUS, G0A6130WEU, G0A6130WUK

ThinkPad T14s Gen 6 (Intel)

Performance

Processor

Intel V Series Core Ultra 5/7 Processor (Series 2)

AI PC Category

Copilot+ PC

AI Performance

Up to 118 overall TOPS

Operating System*

Windows 11 Pro
Windows 11 Home
Linux
Ubuntu Linux

NPU

Integrated Intel AI Boost, up to 48 TOPS

Graphics

Intel Arc Graphics 130V (integrated)
Intel Arc Graphics 140V (integrated)

Memory

32GB LPDDR5x-8533 MoP memory, soldered

Storage^{1 2}

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

²The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Dolby Voice

Camera*

5.0MP + IR discrete, with privacy shutter, Computer Vision on ISP, temporal noise reduction

Battery³

58Wh (up to 23.46 hr) battery, Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁴

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, touch, Eyesafe, 3M DBEF5
- 500nits, 100% sRGB, low power

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, Copilot key, backlight

Touchpad

TrackPoint and glass-like Mylar surface 3-button
Trackpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions⁵

Starting at 313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

⁵The system dimensions may vary depending on configurations.

Weight⁶

Starting at 1.28 kg (2.82 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

Carbon fiber hybrid (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*

Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

WWAN*

5G Sub-6 GHz with embedded eSIM*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader
Camera privacy shutter
IR camera for Windows Hello (facial recognition)
Computer Vision-based User Presence Sensing on ISP*

Manageability

System Management*⁷

Intel vPro Enterprise*

⁷Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications^{8 9 10}

ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 10.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹⁰EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

Other Certifications

Intel Evo Platform*
Eyesafe Certified 2.0*
MIL-STD-810H