

100 Mb ST to 100 Mb ST Mode Converter - 1310 nm Compatible, Up to 40 km (24.9 mi.)

MODEL NUMBER: N784-MDC-4STST



Converts a 100 Mbps multimode fiber optic signal to a 100 Mbps singlemode fiber optic signal.

Features

Customizes Your Network Extension over Fiber Optic Cable

This network mode converter works with a variety of ST cables to convert a multimode fiber signal to a singlemode fiber optic signal and extend it to a second network device. The mode conversion allows your network connection to reach hubs, switches and other devices located up to 40 kilometers (24.9 miles) away. The N784-MDC-4STST is ideal for network engineers migrating toward higher-density data centers.

LEDs Indicate Installation Performance and Diagnostic Functions

Easy-to-read LEDs on the side of the mode converter indicate essential status information, including network speed and connection, signal diagnostics and unit power. LEDs indicate when a fiber cable has been severed or another cause of disruption in service has occurred.

Protective Metal Housing Built to Withstand a Variety of Hazards

The rugged metallic case is designed to operate in temperatures ranging from 0 to 70 degrees Celsius (32 to 158 degrees Fahrenheit).

Specifications

OVERVIEW	
UPC Code	037332292407
Product Type	Fiber Mode Converter
Technology	Singlemode; Multimode
Optical Mode	OM3; OM4; OM5; OS2; SM
Mode Type	Multimode; Singlemode
VIDEO	
Signal Range (m)	40000

Highlights

- Customizable converter extends up to 100 Mbps of data via ST ports up to 40 km
- Durable housing withstands operating temperature range of 0° to 70°C
- LEDs indicate fiber connection and various statuses, including data transfer speed
- Quick plug-and-play installation gets your fiber network up and running immediately

Package Includes

- N784-MDC-4STST 100 Mb ST Mode Converter
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A) with 4.5 ft. (1.4 m) cord
- (4) International plug adapters (North America, Europe, U.K., Australia)
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

DISPLAY	
Accessories (Included)	External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 12V 1A)
NETWORK	
Network Ports	ST DUPLEX (FEMALE)
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; Europlug; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V, 50/60 Hz, 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.52
AC Power Adapter Cord Length (m)	1.38
Power Source	AC Adapter
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 12V, 1A
DC Barrel Plug	OD: 5.5 x 2.5 x 11mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	10.00
CONNECTIONS	
Side A - Connector 1	ST DUPLEX (FEMALE)
Side B - Connector 1	ST DUPLEX (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	PWR (ON) Indicates the device is powered. (OFF) Indicates the device is not powered; Link/Act (FX) Fiber Port Link/Action Status LED (ON) Fiber port is linked. (Blink) Fiber port is activated. (OFF) Fiber port is not linked.; SD-Fiber Signal Status LED (ON) Fiber signal is detected, (OFF) Fiber Signal is not detected.; 10G- UTP Port Speed LED (ON) 2.5G–10G, (OFF) 10/100/1000M.; Link (TX) ON- UTP port is linked, (Blink) UTP port is activated
PHYSICAL	
Color	Black
Material of Construction	Metal Shell
Power Cord Color	Black
Housing Color	Black
Shipping Dimensions (hwd / in.)	2.36 x 5.11 x 9.44
Shipping Dimensions (hwd / cm)	6.00 x 13.00 x 24.00
Shipping Weight (lbs.)	0.97
Shipping Weight (kg)	0.44



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / in.)	0.920 x 2.900 x 4.300
Unit Dimensions (hwd / cm)	2.34 x 7.38 x 10.92
Unit Dimensions (hwd / mm)	26 x 95 x 110 mm (1 x 3.74 x 4.3 in.)
Unit Packaging Type	Box
Unit Weight (lbs.)	1.88
Unit Weight (kg)	0.85
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	32° to 158°F (0° to 70°C)
Relative Humidity	5% to 90% RH, Non Condensing
COMMUNICATIONS	
Network Compatibility	100 Mbps (Fast Ethernet)
Network Speed Details	10 Mbps; 100 Mbps
Wavelength	1310nm
Transmission Distance	2 Km to 40Km
IEEE Standards Supported	802.3u; 802.3z
Network Compatibility Details	Singlemode: 1310 nmMultimode: 850 nm
FEATURES & SPECIFICATIONS	
Data Transfer Rate	10 Mbps; 100 Mbps
Mounting Accessory Included	No
Working Mode	Full/Half Duplex
Ethernet Support	No
Auto MDIX Support	No
DIN Mountable	No
Optical Port	ST
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; GS; LPS; TUV; UL; WEEE; cUL
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); IEC 62368-1; UL 62368-1
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.