

Lenovo 100w Gen 5

Designed for business professionals, the new-gen laptop delivers reliable performance for daily workflows. Powered by the Intel® Processor N150, it ensures smooth multitasking, whether you're managing spreadsheets, drafting proposals, or handling virtual meetings. With 128GB of storage, professionals can securely store essential documents and presentations. The device supports up to 8GB LPDDR5-4800 memory, enabling seamless operation across multiple applications. Its lightweight design enhances mobility, making it an excellent choice for consultants, sales teams, and remote workers who need efficiency on the go.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

Experience clarity and precision with the 11.6" HD IPS display, delivering vibrant visuals, ideal for reviewing contracts, analyzing spreadsheets, and video conferencing. The 2W dual stereo speakers, enhanced with Dolby Audio, provide crisp, immersive sound for virtual meetings, client calls, and multimedia presentations in dynamic business settings.

Stay productive throughout the day with the 47Wh battery, supporting Rapid Charge for up to 80% power in one hour. With up to Intel® Wi-Fi 7 (5 Gig) connectivity, business professionals can enjoy seamless collaboration, cloud access, and high-speed data transfers anywhere.

Built with enterprise-grade security, this laptop features a self-healing BIOS, Secure Wipe, and dTPM 2.0 to safeguard sensitive business data. It ensures secure transactions, protects client information, and helps maintain compliance with industry data protection standards.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo 16-inch Laptop Topload T210 Black (ECO)

- High quality, durable and water-repellent fabric for maximum durability
- Conveniently placed compartments and pockets for quick access
- Made of 80% recycled PET on case exterior



PN: GX41L83769

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: GOA6130WUS, GOA6130WEU, GOA6130WUK

Lenovo 100w Gen 5

Performance

Processor
Intel N Series

Operating System*
Windows 11 Pro or Home

Graphics
Intel Graphics (integrated)

Memory¹
4GB LPDDR5-4800, soldered
8GB LPDDR5-4800, soldered

¹Installed memory is actually 6400 but may run at 4800 due to platform limitations.

Storage²
UFS models:
128GB UFS 2.2 on systemboard, one M.2 2242 PCIe 3.0 x2 slot
SSD models:
One drive, up to 256GB M.2 2242 SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Single microphone

Camera*
HD 720p, with privacy shutter

Battery³
47Wh (up to 12.7 hr) battery, Rapid Charge with 65W AC adapter

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
65W USB-C adapter, PD 3.0

Design

Display⁴
11.6" HD (1366x768) IPS Anti-glare 16:9, 250nits, 50% NTSC

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, Copilot key

Touchpad
Mylar surface touchpad
60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions⁵
287 x 200 x 19.75 mm (11.3 x 7.9 x 0.78 inches)

⁵The system dimensions may vary depending on configurations.

Weight⁶
Around 1.23 kg (2.71 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color
Slate grey

Case material
PC-ABS (top)
PC-ABS (bottom)

Connectivity

WLAN + Bluetooth*
802.11ax (Wi-Fi 6E), Bluetooth 5.3

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-C (USB 5Gbps / USB 3.2 Gen 1), with USB PD 45-65W
1x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 45-65W & DP
1x HDMI 1.4
1x Headphone / microphone combo jack (3.5mm)

Docking
Docking support via USB-C

Security & Privacy

Security
Discrete TPM 2.0
Kensington Nano Security Slot
Camera privacy shutter

Environmental

Material
85% recycled ABS C cover frame
50% recycled PC ABS D cover
48% recycled TPU D cover fee
90% recycled PCC plastic
30% recycled magnets
90% recycled PCC plastic
80% recycled FSC Carton
80% recycled FSC accessory tray
90% ocean bound plastic bag
100% recycled dry-pressed pulp cushion

Certifications

Green Certifications^{7 8}
ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

Other Certifications
ASTM F963*
MIL-STD-810H military test passed