

# Lenovo 13w 2-in-1 Gen 3

Powered by the Intel® Core™ processor, the chic Lenovo 13w 2-in-1 Gen 3 delivers a significant upgrade in both performance and efficiency, making it the perfect choice for educators and administrators wanting enhanced productivity. The integrated Intel Graphics accelerates processing speeds and optimizes multitasking while working on complex learning applications. With a long-lasting 54.7Wh battery supporting rapid charge, professionals can enjoy up to 15.32 hours of extended use. Additionally, its lightweight design and effortless transitions between laptop, tablet, and tent modes provide maximum flexibility and mobility,



## Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

Virtual collaboration has never been clearer, thanks to the high-resolution 5MP user-facing camera, front-facing Dolby stereo speakers and AI-enhanced microphones. Whether you're using it in laptop or tablet mode, the garaged stylus provides precise input whenever needed. Plus, Lenovo's integrated pen technology turns any touch interaction into a seamless, natural writing and sketching experience.

The device features a 13.3" 400-nit display with cutting-edge Dual Brightness Enhancement Film (DBEF5) technology—an industry first. This innovation boosts brightness by 33%, reduces power consumption by 16%, and minimizes eye strain, delivering a brilliant, energy-efficient visual experience.

Online collaboration and immersive learning are more seamless than ever with a high-resolution 5MP user-facing camera, Dolby stereo speakers, and AI-driven mic enhancements that minimize background noise for crystal-clear communication.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



## Accessories

---

### ThinkPad USB-C Wireless Compact Mouse

- Seamless 4-way scrolling (left, right, up, and down) and on-the-fly adjustable DPI controls.
- Plug and play 2.4 GHz USB C wireless dongle
- Supports Lenovo USB A or USB C Unified Pairing Receiver



PN: With Battery : 4Y51D20848 Without Battery : 4Y51D20849

---

### Lenovo USB-C Slim Travel dock

- Effortless Portability for Travelers
- Rapid Data Transfer and Peripheral Connectivity
- Immersive 4K Display Support



PN: ROW: 4XT1N40212, US: 4XT1N40213

---

# Lenovo 13w 2-in-1 Gen 3

## Performance

### Processor

Intel U-series, 13th Gen U Series Core i5 and Core Processor (Series 1)

### Operating System\*

Windows 11 Pro or Home\*

### Graphics

Intel Graphics (integrated)  
Intel UHD Graphics (integrated)  
Intel Iris Xe Graphics eligible (Integrated)

### Memory<sup>1</sup>

Up to 16GB DDR5-4800 offering, 1x Soldered + 1x SODIMM

<sup>1</sup>Installed memory is actually 5600 but may run at 4800 due to platform limitations.

### Storage<sup>2</sup>

Up to two M.2 PCIe NVMe SSD  
M.2 2242 SSD up to 512GB

<sup>2</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

### Audio\*

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Audio  
Dual-microphone array or single + dual microphones

### Camera\*

Front 5.0MP, with privacy shutter  
Front 5.0MP, with privacy shutter; rear 5MP  
Front FHD 1080p + IR, with privacy shutter  
Front FHD 1080p + IR, with privacy shutter; rear 5MP

### Battery<sup>3</sup>

54.7Wh battery (up to 15.32 hr), Rapid Charge with 65W AC adapter

<sup>3</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter\*

65W USB-C adapter, PD 3.0

## Design

### Display<sup>4</sup>

13.3" WUXGA (1920x1200) IPS Glossy 16:10, 300nits, 45% NTSC, 60Hz, Corning Gorilla Glass, anti-fingerprint, touch

<sup>4</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Multimode

Laptop, stand, and tablet modes supported by 360° hinge

### Pen\*

Lenovo Integrated Pen\*

### Keyboard

6-row, Copilot key  
backlight\*

### Touchpad

Mylar surface touchpad  
60.5 x 104 mm (2.38 x 4.09 inches)

### Dimensions<sup>5</sup>

303 x 219.5 x 18.35 mm (11.93 x 8.64 x 0.72 inches)

<sup>5</sup>The system dimensions may vary depending on configurations.

### Weight<sup>6</sup>

Around 1.45 kg (3.2 lbs)

<sup>6</sup>The system weight is approximate and may vary depending on configurations

### Color

Luna grey

### Case material

Aluminium (top), PC-ABS (bottom)

## Connectivity

### WLAN + Bluetooth\*

802.11ax (Wi-Fi 6E), Bluetooth 5.3

### Ports

1x HDMI 2.1, up to 4K/60Hz  
2x USB-A (USB 5Gbps / USB 3.2 Gen 1)  
2x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 45-65W & DP  
1x Headphone / microphone combo jack (3.5mm)

### Docking

Docking support via USB-C

## Security & Privacy

### Security

Discrete TPM 2.0  
Kensington Nano Security Slot  
Touch style fingerprint reader on power button\*  
Camera privacy shutter  
IR camera for Windows Hello (facial recognition)\*

## Environmental

### Material

50% recycled aluminum A cover  
50% recycled PC ABS D cover  
30% recycled PCC keycaps  
100% recycled ocean bound plastic touchpad  
90% recycled PCC plastic  
25% recycled magnets  
90% recycled PCC plastic  
80% recycled FSC Carton  
80% recycled FSC accessory tray  
90% ocean bound plastic bag  
100% recycled dry-pressed pulp cushion

## Certifications

### Green Certifications<sup>7 8</sup>

ENERGY STAR 8.0\*  
ErP Lot 6/26  
RoHS compliant

<sup>7</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>8</sup>EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

### Other Certifications

MIL-STD-810H military test passed (23 test items)