

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced Metered, 2U, 3 Phase, 208V, 17.3kVA 60A, 18 Outlets

APDU11455ME

Main

Color	Black
Product or Component Type	PDU
PDU Type	Metered
Rated power in VA	17300 VA

Complementary

Input Voltage	208 V AC 3 phase
Height	3.3 in (85 mm)
Width	17.4 in (443 mm)
Output Voltage	208 V AC 3 phase
Depth	29.5 in (750 mm)
Product Weight	34.6 lb(US) (15.7 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	IEC 309 60 A IEC 309 100 A
Mounting Mode	Rack-mounted
Rack units	2U
Mounting position	Horizontal
Input current limits	60 A
Input Frequency	50/60 Hz
Plug standard	IEC 60309
Outlet type and quantity	9 C13/C15/C19/C21 9C13/C15

Environment

IP Degree of Protection	IP44
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Relative Humidity	5...90 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-4...140 °F (-20...60 °C)
Storage Relative Humidity	5...95 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage altitude	0...50000 ft (0...15240 m)
------------------	----------------------------

Ordering and shipping details

GTIN	731304775669
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	37.008 in (94 cm)
Package 1 Width	23.6 in (60 cm)
Package 1 Length	6.5 in (16.5 cm)
Package weight(Lbs)	48.9 lb(US) (22.2 kg)



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
SCIP Number	7547f066-9302-46d9-96e9-461928dd6901
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
PVC free	No
Silicon free	Yes

Use Longer

Lifetime extension	
Repair	No
Upgradeability	Yes

Use Again

Repack and remanufacture	
Take-back	No

Image of product / Alternate images

Alternative

