



## SmartFit™ EQ Adjustable Multi-Angle Laptop Stand

Part Number: K50427WW/NA | UPC Code: 0 85896 50427 6

Elevate your  
workspace  
comfort to  
new heights.

Professionals working in compact office spaces often face challenges when using multi-monitor setups featuring a laptop as one of the displays. Limited desk space can lead to discomfort, poor posture, and decreased productivity, making it difficult to maintain an ergonomic workspace.

The SmartFit™ EQ Adjustable Multi-Angle Laptop Stand addresses these issues. It offers six customizable height and angle combinations to support proper ergonomic viewing angles and uses dual locking latches to ensure stability and simplify adjustments. Its durable and compact design not only conserves space but also conveniently folds flat when not in use.

This stand enhances comfort and efficiency, making it an ideal solution for maximizing productivity in small workstations.

- Supports proper ergonomic positioning
- Riser is composed of 75% post-consumer recycled (PCR)
- Ships in FSC® certified packaging
- Tested and recommended by the German IGR Institute for Health and Ergonomics
- Accommodates 13" to 16" laptops and MacBooks
- 6 pre-set height and angle combinations
- Anti-slip silicone foot pads and locking latch
- Space-saving design folds flat when not in use
- No assembly required
- 2-year limited warranty



## SmartFit™ EQ Adjustable Multi-Angle Laptop Stand

Part Number: K50427WW/NA | UPC Code: 0 85896 50427 6



### SmartFit™ – Comfort Made Easy

Supports proper ergonomic eye-level viewing angles, as well as improved neck and shoulder alignment. Uses data-driven research and a color-coded fitting chart to support quick and intuitive height-setting.



### Sustainability Focused

Made from durable, high-quality plastic containing 75% post-consumer recycled content and shipped in FSC® certified packaging.



### Flexible Height and Angle Adjustments

Offers six pre-set height (up to 14.88in/378mm) and angle combinations to simplify positioning, support better posture, and reduce strain during long work sessions.



### Ergonomist Approved

Tested and recommended by the German IGR Institute for Health and Ergonomics, in accordance with DIN 26800 EN ISO 15537. Designed to enhance comfort and improve posture whether sitting or standing at your desk.



### Durable and Stable Construction

Supports laptops and MacBooks from 13" to 16", up to 6.6lbs(3kg). Anti-slip rubber feet and locking latches keep the laptop and riser securely in place while you work.



### Space-Saving Design

This laptop riser occupies minimal desk space (9.96 x 10.16in/253 x 258mm), making it an ideal choice for small or compact workstations.



### Easy to Use

No assembly required, quickly folds for easy storage, and offers dual levers for stable height adjustments.



### Improved Thermals

Raising your laptop helps keep it cooler and reduces strain on the battery and internal parts.

## SmartFit™ EQ Adjustable Multi-Angle Laptop Stand

Part Number: K50427WW/NA | UPC Code: 0 85896 50427 6

### Material Specifications

Platform & arm	PCR ABS
Axles and nuts	Nickel-plated steel
Anti-slip feet	TPE

### Product Dimensions

Unit Dimensions	44.0 x 253.0 x 258.0mm (1.77 x 9.96 x 10.16in)
Unit Weight	745g (26.28oz)
Color	Black
Footprint	253.0 x 258.0mm (9.96 x 10.16in)
Adjustable height	1. 0°: 44mm (1.73in) 2. 30°+30°: 126mm (4.96in) 3. 30°+60°: 240mm (9.45in) 4. 30°+90°: 317mm (12.48in) 5. 60°+60°: 185mm (7.28in) 6. 60°+90°: 301mm (11.85in) 7. 60°+120°: 378mm (14.88in)
Maximum load	3kg (6.6lbs)

### Packaging Dimensions

Packaging Style	K50427WW (B2B: FSC®-Certified); K50427NA (Retail)
Unit Packaging Dimensions	265 x 257 x 48mm (10.43 x 10.12 x 1.89in)
Unit Packaging Weight	K50427WW: 843.9g (29.77oz) K50427NA: 906.3g (31.97oz)
Units in a Master Carton	6 Units
Master Carton Dimensions	275 x 270 x 315mm (10.83 x 10.63 x 12.40in)
Master Carton Weight	K50427WW: 5.60kg (12.35lbs) K50427NA: 5.97kg (13.16lbs)
Packaging Content	1 x Laptop Stand 1 x Warranty Card 1 x Instruction Guide

### Environmental

Storage temperature	-20 to 60°C (-4 to 140°F)
Relative Humidity	58% RH

### Country Of Origin, Regulatory, and Warranty

Country of Origin	China
Warranty	Limited 2-Year Warranty
Certifications & Compliance	Reach, RoHS, RSL



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries. © 2025 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. K25-24049p

# Kensington

The Professionals' Choice™