

Product data sheet

Specifications



APC Smart-UPS On-Line, 5kVA, Rackmount 5U, 208V, 12 5-20R+2 L6-20R+2 L6-30R NEMA, Network Card+SmartSlot, W/ rail kit, W/ transformer 208V to 120V [TAA]

SRT5KRMXLT-5KTF-A

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V AC 1 phase
Other Input Voltages	220 V
Input Connection Type	NEMA L6-30P
Efficiency at full load	100...275 V adjustable (half load)
Input Frequency	40 - 70 Hz auto-sensing
Output voltage	208 V AC 1 phase
Other Output Voltages	220 V
Rated power in W	4800 W
rated power in VA	5000 VA
output connection type	12 NEMA 5-20R 2 NEMA L6-20R 2 NEMA L6-30R
Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	5000 VA
Max Configurable Power (Watts)	4800 W
Topology	On-Line
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Lead-acid internal included
Emergency Power Off (EPO)	Yes
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

UPS connectivity	Serial port USB port Available expansion slot Pre-installed network management card 3
Surge energy rating	480 J
Number of rack unit	5U
Cable length	10.007 ft (3.05 m)
Number of cables	1
color	Black
Height	8.6 in (218 mm)
Width	17.008 in (432 mm)
Depth	28.3 in (719 mm)
Net Weight	217.99 lb(US) (98.88 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal
Mounting mode	Rack-mounted with included kit
Provided equipment	Documentation CD Rack mounting hardware Rack Mounting brackets Rack Mounting support rails User Manual USB cable Warranty card Web/SNMP Management Card
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	High density
Redundant	No
Range of Product	Smart-UPS On-Line
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	ENERGY STAR V2.0 (USA) BAA compliance
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dBA
Online Thermal Dissipation	1047 Btu/h

Operating altitude	0...10000 ft
--------------------	--------------

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Battery Voltage	192V
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	1.5 h
RBC Quantity	1
Battery Life	3...5 year(s)
Replacement battery	APCRBC140 
Battery Charge Power (Watts)	556 W rated

Ordering and shipping details

GTIN	731304772170
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	23.0 in (58.4 cm)
Package 1 Width	37.8 in (96.0 cm)
Package 1 Length	24.5 in (62.2 cm)
Package weight(Lbs)	260.1 lb(US) (118.0 kg)

Compliance

Compliance	TAA Compliant BAA Compliant via COTS
------------	---

Contractual warranty

Warranty (in months)	36 UPS 24 Battery
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	683 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	669 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	7 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0.1 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	65
Circularity Profile	End of Life Information
Removable battery	No
Take-back	Yes

Technical Illustration

Dimensions



Image of product / Alternate images

Alternative

