



## AI PC for hybrid productivity and IT simplicity

Power through demanding tasks with the highly configurable HP EliteBook 6 G2i, a 14-inch HP Copilot+ PC.[4] Long battery life, embedded HP Wolf Security[5], and AI-enhanced[3] performance deliver a seamless, secure experience wherever work takes you.



### AI power meets enterprise precision

Drive innovation and maximize output with this highly secure, easily managed 14-inch AI-enhanced PC.[3]

### See all the details with this brilliant display

See more vertical content in a surprisingly small footprint and reduce the need to scroll on the 14-inch display featuring a 16:10 aspect ratio.[7]

### Protection before the threat

HP Wolf Security for Business creates a hardware-enforced, always-on, resilient defense.[5]

## Featuring

### HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [1]

### Intel® powers PCs next-gen AI

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor with an NPU purposely built for the next era of AI software. Three compute engines manage AI workloads deliver long battery life, and powerful graphics. [2]

### Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7. [6]

### Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [9]

### HP Sure Sense

Malware is evolving rapidly beyond traditional antivirus capabilities. Protect your PC against never-before-seen attacks with HP Sure Sense, which combines behavioral analysis with advanced AI techniques to provide exceptional protection. [10]

## Specifications

<b>Operating System Software</b>	Windows 11 Pro <sup>[1]</sup>
<b>Product Color Description (fixed)</b>	Pike silver aluminum
<b>Processor Family</b>	Intel® Core™ Ultra 5 processor
<b>Processor Name</b>	Intel® Core™ Ultra 5 322 (up to 4.4 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 6 cores, 6 threads) <sup>[6,7]</sup>
<b>Standard Memory Description 01</b>	16 GB DDR5-5600 MT/s (2 x 8 GB)
<b>Memory Slots</b>	2 SODIMM
<b>Hard Drive Description (01)</b>	512 GB PCIe® NVMe™ M.2 SSD
<b>Memory Card Device</b>	1 Smartcard reader
<b>Graphics Card Segment 01</b>	Integrated
<b>GScardseg 01 Available Card 01</b>	Intel® Graphics
<b>Display Description (metric)</b>	35.6 cm (14") diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 300 nits, 45% NTSC
<b>Display Description</b>	14" diagonal, WUXGA (1920 x 1200), IPS, anti-glare, 300 nits, 45% NTSC <sup>[12,14,15,16,17]</sup>
<b>Audio Features</b>	Audio by Poly Studio, dual stereo speakers, dual microphones enhanced by AI noise reduction
<b>Product Dimensions (metric)</b>	31.86 x 22.43 x 1.1 cm (minimum front); 31.86 x 22.43 x 1.7 cm (minimum rear); 31.86 x 22.43 x 1.15 cm (maximum front); 31.86 x 22.43 x 1.75 cm (maximum rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Product Dimensions (imperial)</b>	12.54 x 8.83 x 0.43 in (minimum front); 12.54 x 8.83 x 0.67 in (minimum rear); 12.54 x 8.83 x 0.45 in (maximum front); 12.54 x 8.83 x 0.69 in (maximum rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Weight (metric)</b>	Starting at 1.4 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Weight (imperial)</b>	Starting at 3.09 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Keyboard</b>	Spill-resistant, backlit keyboard
<b>Pointing Device</b>	Clickpad with multi-touch gesture support, taps enabled as default
<b>Sensors</b>	HP Sure Platform; Thermal sensor; HP Tamper Lock; Hall effect sensor <sup>[12,44]</sup>
<b>Integrated Camera</b>	FHD camera with integrated dual array microphones
<b>External I/O Ports</b>	1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45; 1 nano security lock slot; 2 USB Type-A 5Gbps signaling rate (powered); 2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1) <sup>[13]</sup> <i>(HDMI cable sold separately.)</i>
<b>Wireless Technologies</b>	Intel® Wi-Fi 7 BE211 (2x2) and Bluetooth® 6.0 wireless card
<b>Power Supply Required</b>	HP 65 W USB Type-C® GaN power adapter <sup>[20]</sup>
<b>Battery Type</b>	HP Long Life 3-cell, 56 Wh Li-ion
<b>Sustainability Specifications</b>	At least 30% recycled metal; Product Carbon Footprint; HP paper-based packaging is from recycled or certified sources; At least 30% post-consumer recycled plastic; At least 30% ocean-bound plastic; Low halogen; Bulk packaging available; External power supply 90% efficiency
<b>UPC Number</b>	826581111696
<b>Manufacturer Warranty</b>	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <a href="http://www.hp.com/go/cpc">http://www.hp.com/go/cpc</a> .

## Top Recommended Displays, Accessories and Services

---

### Backpacks

HP Travel 18 Liter 15.6 Iron Grey Laptop Backpack	6H2D9AA
---	---------

---

### Topload Bags

HP Renew Business 14.1-inch Laptop Bag	3E5F9AA
--	---------

---

### Sleeves

HP Renew Executive 14-inch Laptop Sleeve	6B8Y3AA
--	---------

## Messaging Footnotes

- [1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.
- [2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors. ISV solutions are sold separately and may require a subscription and NPU.
- [3] Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.
- [4] On some devices, some Copilot+ PC experiences require free updates continuing to roll out from Microsoft. Timing varies by device and region. See [aka.ms/copilotpluspcs](http://aka.ms/copilotpluspcs). Copilot is NOT available in China, Russia, Belarus, and embargoed regions Cuba, Iran, North Korea, Crimea.
- [5] HP Wolf Security for Business requires Windows 10 or 11 Pro and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features.
- [6] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.
- [7] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [9] HP Sure Click requires Windows 10 and higher. See [https://bit.ly/2PrLT6A\\_SureClick](https://bit.ly/2PrLT6A_SureClick) for complete details.
- [10] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

## Technical Specifications Footnotes

- [1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.
- [6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- [7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.
- [12] Optional feature must be configured at the time of purchase.
- [13] USB 20Gbps speed is not available with Thunderbolt™ 4.
- [14] Resolutions are dependent upon monitor capability, and resolution and color depth settings.
- [15] HP Sure View integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.
- [16] Actual brightness will be lower with touchscreen or Sure View.
- [17] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [20] Availability may vary by country.
- [44] HP Tamper Lock can be Enabled/disabled by customers or IT administrator with administrator authority.

---

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Thunderbolt and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

