

Product data sheet

Specifications



APC NetShelter SX Server Rack
Gen 2, 52U, 2436H x 750W x
1200D mm, w/ Sides, Black [TAA]

AR3358B2

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	52U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels
Range of Product	NetShelter SX Enclosures

Physical

Height	95.9 in (2436 mm)
Width	29.5 in (750 mm)
Depth	47.2 in (1200 mm)
Net Weight	441.50 lb(US) (200.26 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.3 in (1048 mm)
Minimum Mounting Depth	11.3 in (286 mm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 lb(US) (1020.6 kg) dynamic 3750 lb(US) (1701.0 kg) static

Conformance

Standards	UL 2416
-----------	---------

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

GTIN	731304753490
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	100.9 in (256.3 cm)
Package 1 Width	33.9 in (86.1 cm)
Package 1 Length	52.09 in (132.3 cm)
Package weight(Lbs)	512.53 lb(US) (232.48 kg)

Compliance

Compliance	TAA Compliant BAA Compliant via COTS
------------	---

Contractual warranty

Warranty (in months)	60
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	705 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 241 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	69 kg CO2 eq.
Carbon footprint of the installation phase [A5]	27 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	557 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	97
Circularity Profile	No need of specific recycling operations
Removable battery	No
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features




Image of product / Alternate images

Alternative



