

2U 19in Steel Horizontal Wall Mountable Server Rack

RK219WALVO / RK419WALVO

DE: Bedienungsanleitung - de.startech.com
 FR: Guide de l'utilisateur - fr.startech.com
 ES: Guía del usuario - es.startech.com
 IT: Guida per l'uso - it.startech.com
 NL: Gebruiksaanwijzing - nl.startech.com
 PT: Guia do usuário - pt.startech.com

Packaging Contents

- 1 x RKx19WALVO mountable server rack
- 8 x #10-32 Cage Nuts and Screws (16 x for RK419WALVO)
- 1 x Installation Guide

Installation

To affix the wall-mountable rack to a wall, there are 4 anchor points on the rear. Disassemble the top cover of the rack, by removing the two screws from either side of the cover. Once removed, all four anchor points should be accessible.



Use the appropriate screws or bolts for mounting heavy equipment to the specific type of wall. Please observe proper safety procedures and use the appropriate tools.

The front mounting brackets can be easily adjusted to three different depths, depending on the equipment or application. Remove the two screws that hold each bracket and move them to one of the other mounting points.



*actual product may vary from photos

Specifications

	RK219WALVO	RK419WALVO
Colour	Black	
Material	SPCC (1.6mm thick)	
Mounting Hole Type	Square	
Internal Height	2U	4U
Internal Mounting Width	19in	
Maximum Weight Capacity	27.7kg / 62.22lbs	
External Dimensions (D x W x H)	118.0mm x 505.0mm x 553.0mm	210.0mm x 505.0mm x 553.0mm
Net Weight	7960g	10960g
Standards	EIA RS-310D	
Certifications	RoHS	

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.