

ThinkPad L16 Gen 2 (Intel)

Unlock new AI experiences with this ThinkPad featuring Intel® H or U Series Core Ultra 5 / 7 Processor, designed to provide a seamless balance of power and efficiency, ideal for business professionals who need to stay efficient and agile while on the go. With up to 64GB DDR5-5600 memory, the laptop ensures lightning-fast data transfer speeds and smooth multitasking, enabling professionals to run multiple applications simultaneously without any slowdowns. Additionally, the inclusion of up to 2TB SSD storage offers vast space for critical files, projects, and applications, with rapid read and write speeds, reducing load times and enhancing overall productivity.



Redefining possibilities with powerful performance and groundbreaking on-device AI


The integration of 2W dual Dolby Atmos® stereo speakers delivers immersive audio, making virtual meetings, presentations, and multimedia consumption more engaging. An optional 5.0MP + IR camera provides crystal-clear video quality for video conferencing, along with advanced facial recognition capabilities for secure, hands-free login.

Whether working on a project deadline or managing a client presentation, the 57Wh Rechargeable Li-ion Battery with rapid charge support ensures the laptop allows professionals to work confidently, without worrying about constant recharging.

Harness the power of Intel® vPro® Enterprise with its advanced software control capabilities, allowing seamless remote management, enhanced security, and streamlined IT operations for maximum productivity and efficiency.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: GOA6130WUS, GOA6130WEU, GOA6130WUK

Lenovo Go Wireless Vertical Mouse

- 6-button mouse including 2 programmable side buttons and an IR sensor
- True Ergonomic vertical design with a 45-degree vertical grip made from treated cork material
- 800, 1600, 2400 adjustable DPI and 2.4 GHz wireless dongle connection



PN: 4Y51C33792

ThinkPad L16 Gen 2 (Intel)

Performance

Processor

Intel H or U Series Core Ultra 5/7 Processor (Series 2)

AI PC Category

AI PC

AI Performance

Up to 96 overall TOPS

Operating System*

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Linux

NPU

Integrated Intel AI Boost, up to 13 TOPS

Graphics¹

Intel Graphics (integrated)
Intel Arc 140T GPU (integrated)

¹Intel Arc graphics only available on select H-series Intel Core Ultra processor powered systems with at least 16GB of system memory in a dual-channel configurations, otherwise it will function as Intel Graphics.

Memory²

Up to 64GB DDR5-5600, 2x SO-DIMM

²The max memory is based on the test results with current Lenovo memory offerings.

Storage³

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, Elevoc Voice

Camera*

HD 720p, with privacy shutter
5.0MP + IR discrete, with privacy shutter, temporal noise reduction

Battery⁴

46.5Wh or 57Wh battery, Rapid Charge

⁴Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁵

16" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 60Hz
- 400nits, 45% NTSC, 60Hz, Eyesafe, touch
- 500nits, 100% sRGB, 60Hz, low power, Eyesafe

⁵IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, numeric keypad, Copilot Key, optional backlight

Touchpad

TrackPoint and Mylar surface TrackPad
67.6 x 115 mm (2.66 x 4.53 inches)

Dimensions⁶

357.2 x 253.4 x 10.96/19.67 (front/rear), 24.75(maximum) mm
14.06 x 9.98 x 0.43/0.77 (front/rear), 0.97 (maximum) inches

⁶The system dimensions may vary depending on configurations.

Weight⁷

Starting at 1.79 kg (3.96 lbs)

⁷The system weight is approximate and may vary depending on configurations

Color

Black

Case material

PC-ABS (top), PC-ABS (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth*

Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

WWAN*

4G LTE CAT6 with embedded eSIM*

NFC

Near Field Communication*

Ports

1x USB-A (Hi-Speed USB / USB 2.0)
2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Ethernet (RJ45)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Manageability

System Management*

Intel vPro Enterprise*

Certifications

Green Certifications^{8 9 10}

EPEAT Gold Registered
ENERGY STAR 9.0
ErP Lot 6/26
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration (self-declaration).

⁹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹⁰EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Eyesafe Certified 2.0*