

Product data sheet

Specifications



Security and Environmental Appliance, NetBotz, Rack Mount, 750 [TAA]

NBRK0750TAA

Overview

Presentation	The NetBotz Rack Monitor 750TAA provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes, from single-rack edge networks to large data centers.
Lead time	Usually in Stock

Main

Product or Component Type	Industrial rack PC
Range of Product	Netbotz
Number of rack unit	1U
Communication Port Protocol	A-Link DHCP HTTPS IPv4 SNMP v1 SNMP v3 SSH v2 TCP/IP
Provided Equipment	Rack Mounting brackets Temperature/Humidity Sensor USB cable
Product Compatibility	Rack Sensor Pod 150 Room Sensor Pod 155

General

Camera Frame Rate	Up to 30fps
Display Resolution	Up to 1280x1024
APC Universal Sensors Supported	0-5V Door contact Dry Contact Humidity Smoke Fluid Spot Leak Temperature Vibration
Number of Universal Sensor Ports	6
Number of Sensor Pods Supported	12
Number of Universal Sensors Supported	78

Physical

Color	Black
Height	1.7 in (4.3 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	17.008 in (43.2 cm)
Depth	7.008 in (17.8 cm)
Net Weight	5.40 lb(US) (2.45 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted
Mounting position	Horizontal

Conformance

Standards	CSA C22.2 No. 60950-1-03 FCC Part 15 class A ICES-003 UL 60950-1
Product Certifications	2014/30/EU AS/NZS 3548 (C-Tick) Class A CE EMC Directive 2004/108/EC VCCI Class A

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0...15240 m)

Communications & Management

Communication Network Type	RJ-45 10/100/1000 Base-T
----------------------------	--------------------------

Ordering and shipping details

GTIN	731304755784
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	4.8 in (12.1 cm)
Package 1 Width	12.5 in (31.8 cm)
Package 1 Length	21.0 in (53.3 cm)
Package weight(Lbs)	9.19 lb(US) (4.17 kg)

Compliance

Compliance	TAA Compliant
------------	---------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	691 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	43 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.7 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.6 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	639 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	49
Circularity Profile	End of Life Information
Removable battery	No
Take-back	Nej

Image of product / Alternate images

Alternative



