

# INSTALLATION INSTRUCTIONS

## C-DMM-3008 Flip Up Dash Monitor Mount

### 2019 - 2020 Ford Fusion Responder

**TOOLS REQUIRED:**

Ratchet Wrench	Dash panel removal tool	Open End Wrench - 7/16"
7 mm Socket	Phillips screwdriver	Wire cutters

**HARDWARE and PARTS:**

<u>QTY</u>	<u>DESCRIPTION</u>	<u>PART#</u>
1	Upper driver side support bracket	CM009533
1	Upper passenger side support bracket	CM009534
1	Lower passenger side support bracket	CM009554
3	10-32 x 1/2" Machine screw	GSM33118
3	#10 Star washer	GSM31034
1	VESA rotator plate	CM009068
1	PVC washer	CM008582
2	1/4" Plastic washer	CM86600
2	1/4" Steel washer	GSM31005
2	1/4" Nylock nut	GSM30016

**Notes:**

The C-DMM-3000 swivel plate accepts C-MM-301 offset bracket used with C-MM-2XX adaptors. C-MM-2XX series adaptor brackets are not needed for most VESA 75 and other Havis Docking Station mounting applications.

CM009068 VESA rotator plate gives additional positioning options, but is not required depending on mounting preference.

**Always!**

- Read all instructions before installing any Havis, Inc. products.
  - Use hardware provided with install kit

**C-DMM-3008  
Assembly**

**CM009534**

Passenger side upper  
support bracket


**CM009533**

Driver side upper  
support bracket

**CM86600** - 1/4" Plastic washer

**GSM31005** - 1/4" Steel washer

**GSM30016** - 1/4" Nylock nut





View of dash center instrument panel



Carefully remove upper center trim bezel using plastic panel tool.



Attach driver side upper support bracket using OEM upper radio mount screw.  
(7mm socket)



Attach passenger side upper support bracket using OEM upper radio mount screw.  
(7mm socket)



Carefully partially remove lower center and side trim panels. ***It is not necessary to completely remove and unplug panels.***



Attach passenger side lower support bracket to dash using OEM lower radio mount screw.  
(7mm socket)



Reattach lower center and side trim panels.



Reattach upper center trim bezel.



Place DMM main frame onto the support brackets.



Attach frame to upper passenger side support bracket with 10-32 x 1/2" screw and star washer. (Phillips screwdriver)



Attach frame to upper driver side support bracket with 10-32 x 1/2" screw and star washer.



Attach frame to lower passenger side support bracket with 10-32 x 1/2" screw and star washer.



Attach VESA plate to the back of the dock. The gray nylon washer will go between this bracket and the DMM swivel plate.



Determine desired position for your specific computer and attach to DMM swivel plate using nylon washers, steel washers, and nylock nuts. Tighten so that the dock rotates smoothly. (Firm, but not too tight)



Check and adjust positioning as desired. Test for proper latching in closed position.



Route wiring along the side of the DMM flip up frame using wire ties and existing holes. Test up / down and side to side motion to confirm wires have adequate slack and strain relief.



Dock the computer and test.



Installation is now complete.