

# HP OmniBook X FlipNGAI 16-as0001TU (BD5Q8PA)



## AI-boosted brainpower to fuel work and play.

The HP OmniBook X Flip 16 NGAI PC combines AI-powered speed and performance for creative work and entertainment. Its large 16" display[5] adapts to your viewing needs—flat, folded, or flipped—offering vibrant colors from every angle. Designed with a sleek recycled metal[1] chassis and backlit keyboard with large keycaps for an elevated experience.



### AI boosted brainpower for work and play

Intel® Core™ Ultra Processors[2] offer AI boosted brainpower with Copilot+ experiences[3] for work and play.

### Designed to watch and work in 4 different modes

Made from recycled metal[1] and designed to watch and work in any mode—clamshell, tent, tablet, and reverse.

### Watch and work on a dazzling 16" touch display[5].

Everything looks bigger and better on a 16" touch display[5], with vibrant colors and crisp images.

## Featuring

### Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way. [6]

### Intel® Core™ Ultra Processors

Make the hard stuff easy with Intel® Core™ Ultra processors. Accelerate AI experiences across hundreds of apps. [7]

### 16:10 aspect ratio

A 16:10 aspect ratio lets you see more of your content with less scrolling.

### McAfee Premium Individual 30-day trial

Secure your device with award winning antivirus and online protection. Free trial includes secure VPN for privacy and data protection when browsing on public Wi-Fi [8]

### Keyboard contains post-consumer recycled plastic

We're bringing a more thoughtful design to our keyboards by using post-consumer recycled plastic in the design. [9]



## Specifications

<b>Operating system</b>	Windows 11 Home
<b>Product color</b>	Glacier silver
<b>Processor family</b>	Intel® Core™ Ultra 7 processor
<b>Processor</b>	Intel® Core™ Ultra 7 258V (up to 4.8 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 8 cores, 8 threads) [6,7]
<b>Chipset</b>	Intel® integrated SoC
<b>Memory</b>	32 GB LPDDR5x-8533 MT/s (onboard)
<b>Internal Storage</b>	1 TB PCIe® Gen4 NVMe™ M.2 SSD
<b>Product design</b>	Sandblasted anodized finish
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® Arc™ 140V GPU (8GB)
<b>Display</b>	40.6 cm (16") diagonal, 2K (1920 x 1200), multitouch-enabled, IPS, edge-to-edge glass, micro-edge, 400 nits, 62.5% sRGB
<b>Display</b>	16" diagonal, 2K (1920 x 1200), multitouch-enabled, IPS, edge-to-edge glass, micro-edge, 400 nits, 62.5% sRGB
<b>Display size (diagonal)</b>	40.6 cm (16")
<b>Display size (diagonal)</b>	16"
<b>Audio</b>	DTS:X® Ultra; Dual speakers; HP Audio Boost; Poly Studio
<b>Dimensions (W x D x H)</b>	35.6 x 24.55 x 1.53 cm
<b>Dimensions (W x D x H)</b>	14.02 x 9.67 x 0.61 in
<b>Weight</b>	1.88 kg
<b>Weight</b>	4.15 lb
<b>Keyboard</b>	Full-size, backlit, soft gray keyboard
<b>Pointing device</b>	HP Imagepad
<b>Input devices</b>	Accelerometer; Gyroscope; IR thermal sensor
<b>Camera</b>	5MP IR camera with temporal noise reduction and integrated dual array digital microphones
<b>Ports</b>	2 USB Type-A 10Gbps signaling rate; 1 HDMI 2.1; 1 headphone/microphone combo; 1 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery 3.1, DisplayPort™ 2.1, HP Sleep and Charge); 1 USB Type-C® 10Gbps signaling rate (USB Power Delivery 3.1, DisplayPort™ 1.4a, HP Sleep and Charge) <sup>[19]</sup>
<b>Package dimensions (W x D x H)</b>	8 x 42.3 x 30.3 cm
<b>Package weight</b>	3.19 kg
<b>Wireless</b>	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card
<b>Power supply type</b>	65 W USB Type-C® power adapter
<b>Battery type</b>	4-cell, 68 Wh Li-ion polymer ( <sup>[23]</sup> )
<b>Battery life</b>	Up to 15 hours and 45 minutes <sup>[3]</sup>
<b>Battery recharge time</b>	Supports battery fast charge: approximately 50% in 45 minutes <sup>[5]</sup>
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Sustainable impact specifications</b>	Ocean-bound plastic in speaker enclosure(s) and bezel; Recycled metal in cover, keyboard frame, base and hinge cap(s); Keyboard keycaps and scissors contain post-consumer recycled plastic
<b>Security management</b>	Mic mute key; Camera privacy shutter; Trusted Platform Module (Firmware TPM) support
<b>Software included</b>	McAfee Online Protection 30-day trial
<b>Software - Productivity &amp; finance</b>	1 month trial for new Microsoft 365 customers <sup>[24]</sup>
<b>Cloud service</b>	25 GB Dropbox storage for 12 months <sup>[1]</sup>
<b>UPC number</b>	198990911670

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

- [1] Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.
- [2] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of clock speed. Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.
- [3] On some devices, Copilot+ PC experiences require free updates available starting later this year and continuing into 2025. Timing varies by device and region. See [aka.ms/copilotpluspcs](https://aka.ms/copilotpluspcs).
- [5] Display measured diagonally.
- [6] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.
- [7] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance. Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors.
- [8] Internet access required and not included. McAfee is pre-installed on your PC and an account is required for activation. Subscription renewal required after trial period. VPN feature is not available in India, China, Syria or North Korea. McAfee is not compatible with Windows 11 in S mode. You'll need to permanently switch out of S mode. There's no charge to switch out of S mode, but you won't be able to turn it back on.
- [9] Keyboard components contain post-consumer recycled plastic. Percentage of post consumer recycled contained in each component varies by product.

## Technical Specifications Footnotes

- [1] 25 GB of free Dropbox storage for 12 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.
- [3] MobileMark 25 Battery life will vary depending on various factors including product model, configuration, loaded applications, features, use, wireless functionality, and power management settings. The maximum capacity of the battery will naturally decrease with time and usage. See <https://bapco.com/products/mobilemark-25/> for additional details.
- [5] Recharges your battery up to 50% within 45 minutes when the system is off using "shut down" command, using HP adapter provided with the notebook or recommended power adapter disclosed in specifications (see <http://store.hp.com>). After charging has reached 50% capacity, charging speed will return to normal speed. Charging time may vary +/-10% due to System tolerance. Available on select HP products.
- [6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- [7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.
- [19] For best results with HP Sleep and Charge, use a USB charging protocol standard cable or cable adapter with an external device.
- [24] Must activate within 180 days of Windows activation.

---

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

