




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




LEFT VIEW



REAR VIEW



RIGHT VIEW



FRONT VIEW

PANDUIT P/N	WEIGHT
P24D01M-XXYZ	SEE SHEET 2

SPECIFICATION:

1. STANDARD:
- | | |
|-------------------|-----------------------------------|
| UNIT TYPE: | MONITORED INPUT |
| ORIENTATION: | VERTICAL, MID |
| OUTLET QTY&TYPE: | (18) C13, (6) C19 |
| INPUT VOLTAGE: | 100-120/200-240VAC |
| INPUT CURRENT: | 30A (24A DERATED) |
| BREAKER QTY&TYPE: | (3) 20A, DOUBLE-POLE |
| INPUT PHASE: | THREE-PHASE WYE |
| RATED POWER: | 8.6kVA |
| INPUT PLUG: | NEMA L21-30P |
| INPUT POWER CORD: | SEE SHEET 2 FOR PART NUMBER TABLE |
- REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:
NONE


3. ACCESSORIES:
(1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D01M-XX Y Z



BOTTOM VIEW

PLUG/RECEPTACLE BLOCK

PLUG
NEMA L21-30P, 4P 5W
30A, 120/208V MAX RATED INPUT
24A DERATED

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT

RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D01M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P24D01M
01A	09/21/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D01M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN _____
DATE _____
PRINT _____

TITLE: INTELLIGENT SERIES PDU
P24D01M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____

DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)	
0<L<50	±0.5
50<L<250	±1.0
250<L<500	±1.5
500<L<1000	±2.5
1000<L<2000	±4.0

THIRD ANGLE PROJECTION

MATERIAL/COLOR: N/A

DRAWING NUMBER: P24D01M_DC

DRAWN BY: GEORGE DATE: 09/21/2017 CHK: SEAN SCALE: NONE

SHT 1 OF 2 SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D01M	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-BL1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-BL1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-RD1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-RD1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-RD1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-WH1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-WH1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-WH1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-YL1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-YL1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-YL1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-BU1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-BU1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-BU1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-GN1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-GN1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-GN1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-BL2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-BL2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-BL2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-RD2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-RD2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-RD2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-WH2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-WH2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-WH2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-YL2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-YL2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-YL2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-BU2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-BU2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-BU2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg
P24D01M-GN2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"-1.75"]	6.7kg
P24D01M-GN2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"-3.5"]	7.3kg
P24D01M-GN2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 100-120/200-240V/30A/3 PHASE WYE , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"-5"]	7.9kg

B

B

A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN _____
DATE _____
PRINT _____

TITLE
INTELLIGENT SERIES PDU
P24D01M-XYZ
CUSTOMER DRAWING

ITEM REVISION NAME _____

DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)
0<L<50 ±0.5
50<L<250 ±1.0
250<L<500 ±1.5
500<L<1000 ±2.5
1000<L<2000 ±4.0

MATERIAL/COLOR:
N/A

DRAWING NUMBER:
P24D01M_DC

DRAWN BY: GEORGE DATE: 09/21/2017 CHK: SEAN SCALE: NONE

SHT 2 OF 2 SCALE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D01M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P24D01M
01A	09/21/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D01M

2



1