

TrueReach

8K 60Hz Ultra HD 1 to 2
HDMI™ SPLITTER



User Manual
Y10G011-B1



Important safety notice

- 1- Ensure all devices are properly grounded to prevent electric shock. Avoid placing this device near radiators, heat registers, or in direct sunlight.
- 2- Protect the device from exposure to rain or water to prevent potential failures, fires, or electric shocks.
- 3- Place the device on a stable, even surface to prevent malfunctions due to falls.
- 4- Never insert metallic objects into the open parts of this device to avoid the risk of electric shock.
- 5- When using a third-party power supply, ensure it meets the product's specified requirements for safety and compatibility.

Introduction

This TrueReach HDMI Splitter is an 8K HDMI splitter designed to divide one HDMI input signal into two HDMI output signals. Utilizing the latest HDMI 2.1 standard, it supports video signal transmission up to 8K@60Hz/4K@120Hz. With HDR10+, Dolby Vision high dynamic range imaging, and Variable Refresh Rate (VRR) technology, the screen display is exceptionally detailed and smooth. This splitter is versatile and finds wide applications in TV stores, cinemas, outdoor advertising, home entertainment, and more.


Features

- Divides one HDMI input signal into two HDMI display device output signals. Supports resolutions up to 8k@60Hz/4k@120Hz, with downward compatibility.
- Features support for HDR10+, Dolby Vision high dynamic range imaging.
- Includes support for Variable Refresh Rate (VRR) technology.
- Compatible with HDMI 3D technology.
- Offers EDID passthrough and automatic downscaling for optimal signal transmission.
- Provides S/PDIF digital audio separation output capability.
- Allows for firmware upgrading via Micro-USB port for convenient updates.
- Equipped with lightning protection, surge protection, and ESD protection for enhanced durability.
- Supports 7x24 uninterrupted working, ensuring stable and reliable operation.

Package Contents



Splitter x1



DC5V/1A x1




User Manual x1



Grounding
Screw x1


Panel Description



① S/PDIF Out	Connect to the audio device with digital optical audio cable
② Firmware Upgrading	Connect the computer with Micro USB cable for firmware upgrading
③ HDMI Out 1/2	Connect with HDMI display devices Note: To ensure that all monitors can show at their maximum resolution, please connect the monitor with highest resolution to HDMI Output 1, which is configured as the port that can output the maximum resolution (via EDID management).
④ HDMI In	Connect HDMI signal source
⑤ DC5V Power Input	Connect with DC 5V/1A power adapter
⑥ Power Light	Steady on: The power is on
⑦ HDMI Signal Light 1/2	Corresponding to 2 HDMI outputs, the indicator light is steady on when the signal transmission is normal

Installation Procedures

1. Connection Diagrams



2. Connection Instructions

- 1) Connect the splitter HDMI input interface to the device with HDMI signal source output interface via an HDMI cable.
- 2) Connect the splitter HDMI output interface to the display device with HDMI input interface via an HDMI cable.
- 3) If you need to output the audio of the signal source separately, please connect the speaker or power amplifier with S/PDIF audio cable
- 4) If firmware upgrading is required, please connect the computer with a Micro USB cable.
- 5) Connect the power supply, the power indicator is on, and the product starts to work.

FAQ

Q: There is no image output from the display device.

A:

- 1) Please check whether the power supply is connected properly and whether the power indicator is always on.
- 2) Replace the HDMI cable and reconnect it.
- 3) Check whether the input source of the display device is set to the relevant input channel.

Q: The TV shows unstable images, flashing screen, flashing snow.

A:

- 1) Check whether the HDMI cable is firmly connected.
- 2) Reconnect the input signal source to the TV directly, or reset the signal source.
- 3) When transmitting 8K@60Hz HDMI signal, you will need an HDMI2.1 cable.

Q: The TV sound stuck or silent.

A:

- 1) Switch other audio formats.
- 2) Check whether the HDMI cable is firmly connected.

Specifications

Items	Description		
Video signal	HDMI Input	1x HDMI	
	HDMI Output	2x HDMI	
	Compatibility	HDMI 2.1, HDMI2.0, HDMI1.4	
		HDCP 2.3, HDCP2.2, HDCP1.4	
	Resolutions	7680x4320@24/25/30/50/60Hz	
		3840x2160@24/25/30/50/60/120Hz 1080p@24/25/30/50/60/120Hz 720p@50/60/100/120Hz	
	EDID passthrough, auto downscaling		
	HDR10/HDR10+/Dolby Vision		
	HDMI 3D		
	HDMI CEC		
VRR, Free Sync, G-Sync			
Audio signal	S/PDIF Output	LPCM5.1, DTS 5.1, Dolby 5.1	
	HDMI Output	Dolby Atmos, Dolby Digital 7.1CH, Dolby True HD, DTS:X, DTS-HD, LPCM 7.1CH, etc.	
Power	Power Supply	DC5V/1A	
	Power Consumption	< 4W	
Operating Environment	Working temperature	-20 C ~60 C	
	Storage temperature	-30 C ~70 C	
	Humidity	0~90%RH (No condensation)	
Physical Properties	Housing	Iron	
	Weight	200g	
	Color	Black	
	Dimensions	135.0(L)*54.0(W)*16.5(H)mm	

Protection	ESD protection 1a Contact discharge level 2 (±4KV) 1b Air discharge level 3 (±8KV) Implementation of the standard: IEC61000-4-2
	Lightning protection, Surge protection

Contact Information

Corporate Headquarters
12979 Arroyo Ave
San Fernando, CA 91340 - USA

Office: +1 (818) 727-7000
Fax: +1 (818) 875-0002
Email: info@Rocstor.com

Technical Support / RMA
Hours: 9:00 am - 5:00 pm PST
Mon - Fri (excluding holidays)

Sales Info
Hours: 8:00 am - 5:00 pm PST
Mon - Fri (excluding holidays)

Tell: +1 (818) 727-7000 (DOM/INTL)
Fax: +1 (818) 875-0002
Email: support@Rocstor.com

Tell: +1 (818) 727-7000 (DOM/INTL)
Fax: +1 (818) 875-0002
Email: support@Rocstor.com

Corporate, Government and Academic Customers

Our Corporate Sales Team's goal is to help our U.S.A. and Canadian customers find a storage solution that best serves their needs. We will help you determine your best purchasing options. For more information please contact the appropriate department below or call us at +1 (818) 727-7000.

General sales information: sales@Rocstor.com
Corporate sales information: corporate_sales@Rocstor.com
Educational sales information: academic_sales@Rocstor.com
Federal, State & Local government sales information: government_sales@Rocstor.com

Disclaimer

©2024 Rocstr, Inc. Rocstor is registered trademark of Rocstor, Inc. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc. The product name and brand name may be registered trademark of related manufactures.™ and ® may be omitted on the user manual. The pictures in this user manual are just for reference. We reserve the rights to make changes without further notice to a product or system described herein to improve reliability, function or design.