



Environmental Certificates



[Newland](#)

NLP412
NEWLAND | "U" SHAPED DESK WITH 3-STAGE HEIGHT
ADJUSTABLE TABLE

Newland - simple and modular components combining classic design, quality and value to support a wide range of workspace applications. From private offices to open plan, meeting and training spaces, Newland offers functional and practical desking solutions that will stand the test of time.

- L-shaped height adjustable table and credenza with pedestal
- thermally fused laminate top, 1" thick
- 2 mm matching edge
- leveling glides included
- 3-stage base - range of adjustability is 22.6" to 48.2"H
- easy to use up-down controller with digital read-out and four memory programmable positions
- dual motor with 330 lbs. lift capacity
- anti-collision sensor
- standby power consumption 0.1W. Active power consumption 220W
- operates at 1.2" per second
- operating decibel - 42db
- 8' long power cord
- meets applicable ANSI/BIFMA x5.5 standards
- laminate tops covered by Global's lifetime warranty
- five-year warranty on base components including electrical components and motorized parts
- ETL/CETL and Greenguard Certified
- worksurface is dimensioned to allow 1" gap around perimeter in a nominal footprint
- designed for quick and easy assembly
- can be assembled for left or right hand applications

Finish Options:

Laminate finish: Available in all Newland finishes



Package Includes:

NL7029HAT: Rectangular top

MLIR30B: 3-stage height adjustable base

NL4123RHT: Return top

MLIR30R: 3-stage height adjustable return base

NL7224C: Credenza

NL23BBF: Box/box/file pedestal

Specifications:

Weight: 426.5 lbs / 193.46 kg

Volume: 24.65 ft³ / 0.69 m³

Overall Dimensions

72"W x 95"D x 29.6"H
