

ThinkStation P3 Tiny Gen 2

Whether managing projects, developing software, or creating high-end content, this workstation, powered up to one 65W Intel® Core™ Ultra (Series 2) processor, delivers powerful performance tailored for business professionals who demand speed, responsiveness, and efficiency. The discrete GPU options, including the NVIDIA® RTX A1000 or RTX A400, ensure exceptional graphics capabilities for intensive design, rendering, and analytical tasks, while integrated Intel® Graphics offer reliable performance for everyday business applications. Supporting up to 128GB DDR5-6500 memory, this system enables seamless multitasking and ultra-fast data processing, making it ideal for professionals working with large datasets, complex simulations, or creative workflows.



**Elevate Professional Endeavors
with Powerhouse Workstations**

The support for up to four independent displays through onboard DisplayPort, HDMI punch out port 1 (VGA / HDMI® / DP / USB-C®), and punch out port 2 (VGA / HDMI® / DP / Thunderbolt™ 4) allows users to create a highly customized and expansive visual workspace. Whether managing complex data sets, multitasking across various software tools, or presenting content seamlessly, this multi-display support significantly enhances productivity and workflow efficiency.

The robust security features, including a discrete TPM 2.0 chipset provide hardware-based encryption for sensitive data, secure credential storage, and ensures system integrity by preventing unauthorized access at the hardware level. Additionally, 3 x 7 mm Kensington® Security Slot™ offers flexible anchoring options to secure the workstation to a desk or fixed location, effectively deterring theft.

The compact dimensions of 179 x 182.9 x 37mm and weight of 1.4kg (3 lbs) make this 1L Tiny workstation an ideal solution for modern business professionals seeking efficiency without compromising performance. Its ultra-small footprint allows it to fit seamlessly into any workspace, freeing up valuable desk space for greater productivity and organization.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- On-site support if needed
- Normally next business day service
- Agreed appointment times

Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

Lenovo Essential FHD Webcam Gen 2

- Built-in microphones and camera cover
- Smart control with broad compatibility
- Flexible mounting with fast USB setup



PN: 4XC1S15018

ThinkStation P3 Tiny Gen 2

Performance

Processor
Up to one 65W Intel Core Ultra (Series 2) processor

Operating System*
Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Ubuntu Linux LTS
Red Hat Enterprise Linux (certified only)

Graphics¹
Intel Graphics (integrated)
NVIDIA A400
NVIDIA A1000 8GB

¹Intel Arc graphics only available on select H-series Intel Core Ultra processor powered systems with at least 16GB of system memory in a dual-channel configurations, otherwise it will function as Intel Graphics.

Chipset
Intel Q870 chipset

Memory^{2 1}
Up to 128GB (2x 64GB DDR5 CSODIMM)

²The max memory is based on the test results with current Lenovo memory offerings.

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage^{3 2}
Up to 3x M.2 PCIe NVMe SSD

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Design

Dimensions^{6 3}
179 x 182.9 x 37mm (7.05 x 7.2 x 1.5 inches, with rubber feet)

⁶The system dimensions may vary depending on configurations.

³The system dimensions may vary depending on configurations.

Weight^{7 4}
1.4 kg (3 lbs, maximum configuration)

⁷The system weight is approximate and may vary depending on configurations

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet
One onboard Gigabit Ethernet
Additional Ethernet options via PCIe adapter

WLAN + Bluetooth*^{8 5}
Intel Wi-Fi 7 BE200, 802.11be 2x2 Wi-Fi + Bluetooth 5.4

⁸Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Security
Discrete TPM 2.0
Kensington Security Slot, 3 x 7 mm
Chassis intrusion switch

Manageability

System Management*^{9 6}
Intel vPro Enterprise with Intel AMT 16.0*

⁹Intel vPro offers a superset of DASH's defined capabilities.

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications^{10 11 12 7 8}
ENERGY STAR 9.0
EPEAT Gold Registered
RoHS compliant
TCO Certified 10.0

¹⁰The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

¹¹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹²EPEAT is registered where applicable, please see epeat.net for registration status by country.

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications
MIL-STD-810H military test passed