



## Bold performance without the burnout

The new OMEN 16 not only has the power of the latest next-gen Intel®[1] and NVIDIA® components, but it also has the proper thermal innovations to keep them from burning out. Pair that with OMEN AI for maximum possible FPS at the click of a button and Unleashed Mode for that extra boost in performance, and you have our most reliably powerful laptop yet.



### Cooling that keeps up

Handle the heat with high efficiency fans that reduce noise and keeps your laptop cool while you game on.

### Instantly raise your game

Get maximum possible FPS with OMEN AI and boost your power beyond its base limits with Unleashed Mode.

### Next generation of performance

Get the best possible performance with the latest next-gen NVIDIA® GPUs and Intel® Processors[1].

## Featuring

### Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way. [4]

### Smarter. Faster. Lighter

Gaming, creating, AI. Do it all on Intel® Core™ Ultra processors [5]

### Wide Quad Extended Graphics Array Display


Get lost in the captivating definition with 2560 × 1600 pixels. [6]

### Eyesafe® Certified Display

Eyesafe® certified displays meet TÜV low blue light requirements and Eyesafe® standards for protecting your eyes from harmful blue light without distorting colors to reduce eyestrain when working for long periods of time. [7]

### 3ms response time

How fast your display's pixels respond is crucial for a smooth picture. With a 3-millisecond response time, your action-filled content will look crisp and fluid without motion blur. [8]



## Specifications

<b>Operating system</b>	Windows 11 Home
<b>Product color</b>	Shadow black, black chrome logo
<b>Processor family</b>	Intel® Core™ Ultra 7 processor
<b>Processor</b>	Intel® Core™ Ultra 7 255H (up to 5.1 GHz with Intel® Turbo Boost Technology, 24 MB L3 cache, 16 cores, 16 threads) [6,7]
<b>Chipset</b>	Intel® integrated SoC
<b>Memory</b>	24 GB DDR5-5600 MT/s (1 x 24 GB)
<b>Internal Storage</b>	1 TB PCIe® Gen4 NVMe™ M.2 SSD
<b>Product design</b>	Paint finish
<b>Graphics</b>	Discrete
<b>Graphics (discrete)</b>	NVIDIA® GeForce RTX™ 5050 Laptop GPU (8 GB GDDR7 dedicated)
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® Arc™ 140T GPU
<b>Display</b>	40.6 cm (16") diagonal, WQXGA (2560 x 1600), 60-240 Hz, 3 ms response time, IPS, micro-edge, anti-glare, Low Blue Light, 500 nits, 100% sRGB
<b>Display</b>	16" diagonal, WQXGA (2560 x 1600), 60-240 Hz, 3 ms response time, IPS, micro-edge, anti-glare, Low Blue Light, 500 nits, 100% sRGB
<b>Display size (diagonal)</b>	40.6 cm (16")
<b>Display size (diagonal)</b>	16"
<b>Audio</b>	DTS:X® Ultra; Dual speakers; HP Audio Boost; HyperX
<b>Dimensions (W x D x H)</b>	35.75 x 26.9 x 2.37 cm (front); 35.75 x 26.9 x 2.54 cm (rear)
<b>Dimensions (W x D x H)</b>	14.07 x 10.59 x 0.94 in (front); 14.07 x 10.59 x 1 in (rear)
<b>Weight</b>	2.43 kg
<b>Weight</b>	5.36 lb
<b>Keyboard</b>	Full-size, 4-zone RGB backlit, shadow black keyboard with numeric keypad and 26-Key Rollover Anti-Ghosting Key technology
<b>Pointing device</b>	HP Imagepad
<b>Input devices</b>	IR thermal sensor
<b>Camera</b>	HP True Vision 1080p FHD camera with temporal noise reduction and integrated dual array digital microphones
<b>Ports</b>	1 USB Type-A 10Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 1 AC smart pin; 1 HDMI 2.1; 1 headphone/microphone combo; 1 RJ-45; 1 USB Type-C® 10Gbps signaling rate (USB Power Delivery 3.0, DisplayPort™ 1.4, HP Sleep and Charge) <sup>[19,42]</sup>
<b>Expansion slots</b>	2 M.2 (SSD)
<b>Package dimensions (W x D x H)</b>	6.3 x 56.7 x 30.5 cm
<b>Package weight</b>	3.77 kg
<b>Network interface</b>	Integrated 10/100/1000 GbE LAN
<b>Wireless</b>	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
<b>Power supply type</b>	230 W AC power adapter
<b>Battery type</b>	6-cell, 83 Wh Li-ion polymer ([23])
<b>Battery recharge time</b>	Supports battery fast charge: approximately 50% in 30 minutes <sup>[5]</sup>
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Sustainable impact specifications</b>	Ocean-bound plastic in speaker enclosure(s) and bezel; Keyboard keycaps and scissors contain post-consumer recycled plastic
<b>Security management</b>	Camera privacy shutter; Trusted Platform Module (Firmware TPM) support
<b>Software included</b>	McAfee Online Protection 30-day trial
<b>Software - Productivity &amp; finance</b>	1 month trial for new Microsoft 365 customers <sup>[24]</sup>
<b>Cloud service</b>	100 GB Dropbox storage for 3 months <sup>[1]</sup>
<b>UPC number</b>	199764036407

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

[4] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[5] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information. Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, software and other factors.

[6] WQXGA content is required to view WQXGA images.

[7] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. Eyesafe® Display for Low Blue Light is the Display Compliance Test Specification quality. See <https://eyesafe.com> for more details. Display measured diagonally

[8] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower.

## Technical Specifications Footnotes

[1] 100 GB of free Dropbox storage for 3 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.

[5] Recharges your battery up to 50% within 30 minutes when the system is off using "shut down" command, using HP adapter provided with the notebook or recommended power adapter disclosed in specifications (see <http://store.hp.com>). After charging has reached 50% capacity, charging speed will return to normal speed. Charging time may vary +/-10% due to System tolerance. Available on select HP products.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[19] For best results with HP Sleep and Charge, use a USB charging protocol standard cable or cable adapter with an external device.

[24] Must activate within 180 days of Windows activation.

[42] For optimal performance and battery chargeability while gaming and rendering, use the power adapter that ships with the PC. You can use the 100W/20V Type-C adapter or power bank when running light loading tasks. System-off charging is only supported on 20V Type-C adapter or power bank.

---

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

