

Product data sheet

Specifications



APC NetShelter Rack PDU
Advanced Gen 2, Switched
Metered Outlet, 3Phase, 43.5kW
400V 63A or 34.6kW 415V 60A,
560P6, 42 Outlet

APDU11450SM

Overview

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Switched metered outlet

Cord length 9.8 ft (3 m)

Complementary

Input Voltage 415 V 3 phase

Height 71.9 in (1826 mm)

Width 2.2 in (56 mm)

Output Voltage 240 V

Depth 3.0 in (75 mm)

Net Weight 28.0 lb(US) (12.7 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type IEC 60309 60 A 3P+N+PE

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication Port Protocol 1000BASE-T
10/100BASE-T

Line Rated Current 48 A

permissible voltage 200...240 V
346...415 V

Input current limits 60 A

Load Capacity 34600 VA

Input Frequency 50/60 Hz

Outlet type and quantity 21 C13/C15/C19/C21
21C13/C15

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
IP Degree of Protection	IP44
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304752790
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	78.0 in (198 cm)
Package 1 Width	5.2 in (13.2 cm)
Package 1 Length	10.3 in (26.2 cm)
Package weight(Lbs)	34.6 lb(US) (15.7 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Removable battery	No
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



