

ThinkPad T14s Gen 6 (AMD)

Powered by next-generation AMD Ryzen AI 7 PRO 360 processors, the ThinkPad T14s Gen 6 is optimized to elevate productivity and unleash creative expression. It is the first ever x86 next-gen AI PC that offers 50 TOPS and puts you in command of AI processing power. Encased in a sleek and stylish in Eclipse Black chassis, with a refined interior and 16:10 display, this intelligent device offers both brains and beauty. Plus, the redesigned exhaust, new 3M optical solutions and industry-first accessibility features, sets a new standard for the modern workforce.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad T series laptops offer professional-grade durability, powerful performance with good processors, ample memory, and fast SSD storage. They feature robust security features and long battery life for productivity on-the-go.

The impressive 14" WUXGA panel with 88% screen-to-body ratio is made even more extraordinary by 3M's optical solution that amplifies screen brightness to 400nit while lowering power consumption. With the 5MP camera, you'll also be seen by others with crisp, unyielding clarity—elevating every collaboration.

Connectivity will never be an obstruction. With Qualcomm Wi-Fi 7, this device enhances wireless performance and helps professionals stay productive with stable network connectivity, low latency and great bandwidth.

Stacked with up to 12 high-performance "Zen 5" cores, the next-generation AMD Ryzen 7 AI PRO processor offers unparalleled responsiveness and multitasking prowess.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Co2 Offset Service

- Hardware transaction facilitates easy Co2 offset integration.
- Co2 compensation covers production to lifecycle.
- Co2 Offset contributions can be easily tracked and confirmed.

Accessories

ThinkPad Professional 14-inch Topload Gen 2

- Sleek and Sophisticated Design
- Weather-Proof Security with Waterproof Zippers
- Easily Locate Essentials



PN: 4X41M69796

Thinkpad Universal USB-C Smart Dock

- Access to multiple 4K monitors, and blazing-fast data transfers with USB-C and USB-A
- Supports both Thunderbolt™ 3 and 4, USB 4™ and USB-C, and extended compatibility with a wide range of brands and Multi-OS notebooks
- 11+ expansion possibilities in a single quick-release cable for maximum efficiency



PN: 40B20135XX

ThinkPad T14s Gen 6 (AMD)



Performance

Processor
AMD Ryzen AI 7 PRO 300 Series Processor - Strix Point
AMD Ryzen AI 5 / 7 PRO 300 Series Processor - Krackan Point

AI PC Category*
Copilot+ PC

Operating System*
Windows 11 Pro or Home
Fedora or Ubuntu Linux

NPU*
Integrated AMD Ryzen AI, up to 50 TOPS

Graphics
AMD Radeon 840M (integrated)
AMD Radeon 860M (integrated)
AMD Radeon 880M (integrated)

Memory
16GB LPDDR5X-7500, soldered
32GB LPDDR5X-7500, soldered
64GB LPDDR5X-7500, soldered

Storage¹
Up to 1x 1TB M.2 2280 PCIe NVMe SSD

¹The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

Audio*
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Dolby Voice

Camera*
5.0MP, with privacy shutter, temporal noise reduction
5.0MP + IR discrete, with privacy shutter, temporal noise reduction
5.0MP + IR discrete, with privacy shutter, CV on ISP, temporal noise reduction

Battery²
58Wh (up to 17.1 hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0
65W USB-C nano GaN adapter, PD 3.0

Design

Display³
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 3M DBEF5
- 400nits, 45% NTSC, touch, Eyesafe, 3M DBEF5
- 400nits, 100% sRGB, low power
- 500nits, 100% sRGB, low power
- 500nits, 100% sRGB, on-cell touch, ThinkPad Privacy Guard, Eyesafe
14" 2.8K (2880x1800) OLED AGARAS 16:10
- 500nits, 100% DCI-P3, 120Hz VRR, Add-on Film Touch, Dolby Vision, Eyesafe

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio
88%

Keyboard
6-row, spill-resistant, Copilot key, optional backlight

Touchpad
TrackPoint and glass-like Mylar surface 3-button Trackpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions⁴
Starting at 313.6 x 219.4 x 11.43/16.4 (front/rear), 19.75 (maximum) mm;
12.35 x 8.64 x 0.45/0.65 (front/rear), 0.78 (maximum) inches

⁴The system dimensions may vary depending on configurations.

Weight⁵
Strix Point: starting at 1.30 kg (2.86 lbs)
Krackan Point: starting at 1.25 kg (2.76 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color
Black

Case material
Carbon fiber hybrid (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*⁶
802.11be (Wi-Fi 7), Bluetooth 5.3 or 5.4

⁶Bluetooth 5.3 operation requires Windows 11.

WWAN*
4G LTE CAT6 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

NFC
Near Field Communication*

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Security
ThinkShield
Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*
Ultrasonic Human Presence Detection*
Computer Vision-based Human Presence Detection c
ISP*

Manageability

System Management*
DASH*

Environmental

Material
30% recycled Carbon fiber on top cover
90% recycled magnesium on keyboard frame
55% recycled aluminum on bottom cover
85% PCC recycled plastic used in backlit keycaps
90% PCC recycled plastic used in speaker enclosure
90% recycled plastic used in the 58Wh battery frame
90% PCC recycled plastic used in standard 65W adapter
95% PCC recycled plastic used in cable / antenna holders
100% plastic free packaging with FSC certified paper

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2026 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.