

HP ProBook 4 G1i 16 inch Notebook AI PC Wolf Pro Security Edition (D4EC7UT)



Maximize your potential with a resilient, future-ready laptop

The HP ProBook 4 G1i 16-inch Notebook AI PC provides growing businesses with commercial-grade performance, multi-layered endpoint security[6], and durability in an easily upgradeable design. Powered by the latest Intel® processor[2] with 11 TOPS NPU[4] and long battery life, this feature-rich PC is future-ready for long-term productivity and AI exploration.



Designed for thriving business

Easily manage tasks with a powerful Intel® processor[2] featuring an NPU[4] and upgradeable storage and memory.

Hybrid productivity unleashed

Enhance productivity working from home or in the office with the 16:10 aspect ratio[5] on a 16-inch display.

Enterprise-level security

Safeguard your growing business with multi-layered, endpoint security features[6] that help protect your PC and data.

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. ^[1]

Latest Intel® multi-core processor

Configure your HP ProBook CPU for the perfect combination of power, snappy performance, and value. The latest Intel® processor handles multiple work tasks smoothly and reliably with multiple processing cores to divide up the work. ^[2]

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses. ^[3]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6. ^[7]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. ^[9]

Specifications

Operating System Software	Windows 11 Pro
Product Color Description (fixed)	Pike silver
Processor Family	Intel® Core™ Ultra 7 processor
Processor Name	Intel® Core™ Ultra 7 255U (up to 5.2 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 12 cores, 14 threads) [6,7]
Standard Memory Description 01	24 GB DDR5-5600 MT/s (1 x 24 GB)
Memory Slots	2 SODIMM
Hard Drive Description (01)	1 TB PCIe® NVMe™ SSD
Graphics Card Segment 01	Integrated
GScardseg 01 Available Card 01	Intel® Graphics
Display Description (metric)	40.6 cm (16") diagonal, WUXGA (1920 x 1200), touch, IPS, anti-glare, 300 nits, 62.5% sRGB
Display Description	16" diagonal, WUXGA (1920 x 1200), touch, IPS, anti-glare, 300 nits, 62.5% sRGB ^[14,15,16,46]
Audio Features	Audio by Poly Studio, dual stereo speakers, dual array microphones
Product Dimensions (metric)	35.94 x 25.1 x 1.7 cm (rear); 35.94 x 25.1 x 1.09 cm (front) (Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)
Product Dimensions (imperial)	14.15 x 9.88 x 0.43 in (front); 14.15 x 9.88 x 0.67 in (rear) (Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)
Weight (metric)	Starting at 1.74 kg (Weight will vary by configuration. Does not include power adapter.)
Weight (imperial)	Starting at 3.86 lb (Weight will vary by configuration. Does not include power adapter.)
Keyboard	Spill-resistant, backlit keyboard with numeric keypad
Pointing Device	Clickpad with multi-touch gesture support
Sensors	HP Sure Platform; Thermal sensor; HP Tamper Lock; Hall effect sensor ^[11,32]
Integrated Camera	5 MP IR camera
External I/O Ports	1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45; 2 USB Type-A 5Gbps signaling rate (powered); 2 USB Type-C® 20Gbps signaling rate (USB Power Delivery 3.0, DisplayPort™ 1.4, HP Sleep and Charge) ^[21] (Cables are not included.)
Network Interface	Realtek RTL8111HSH-CG GbE
Wireless Technologies	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
Power Supply Required	45 W USB Type-C® adapter ^[19]
Battery Type	HP Long Life 3-cell, 56 Wh Li-ion polymer
Energy Star Certified	ENERGY STAR® certified
Sustainable Impact Specifications	Low halogen; Bulk packaging available; 25% post-consumer recycled plastic; 50% ocean-bound plastic; 50% recycled metal; 100% of HP paper-based packaging is from recycled or certified sustainable sources
UPC Number	(ABA) 199896750554; (ABL) 199896750585
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

Series 5 Pro

HP Series 5 Pro 23.8 inch FHD Monitor - 524pf	9D9L6UT
HP Series 5 Pro 23.8 inch FHD USB-C Conferencing Monitor - 524pm	9E0G9UT
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5AA

Wired Headset

Poly Blackwire 3320 Stereo USB-C Headset +USB-C/A Adapter	8X219AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA

Wireless Headset

Poly Voyager 4320 USB-C Headset +BT700 dongle	76U50AA
---	---------

Backpacks

HP Everyday 16-inch Laptop Backpack	A08KLUT
HP Travel Plus 30L 17-inch Laptop Backpack	A2CE0AA

Topload Bags

HP Everyday 16-inch Laptop Bag	A08KKAA
--------------------------------	---------

Internal ports/Modules/Controllers

HP 4G LTE-Advanced Pro Cat16 WWAN	B8BD2AA
-----------------------------------	---------

Wireless Keyboards

HP 225 Wireless Keyboard	805T1AA
HP 455 Programmable Wireless Keyboard	4R177AA
HP 475 Dual-Mode Wireless Keyboard	7N7B9UT

Wireless Mice

HP 235 Slim Wireless Mouse	4E407UT
HP 435 Multi-Device Wireless Mouse	3B4Q5UT
HP 515 Ultra-Fast Rechargeable Wireless Mouse	9C2F7AA

Port Replicators

HP Universal USB-C Multiport Hub	50H55UT
HP USB-C Travel Hub G3	86S97UT

Power Adapters

HP 65W GaN USB-C Laptop Charger	600Q8UT
HP 110W USB-C Laptop Charger	8B3Y2UT

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] This product includes a one (1) year license of HP Wolf Pro Security Edition which includes HP Sure Click Pro and HP Sure Sense Pro. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP End User License Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/ish_3875769-3873014-16 as modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP Sure Sense Pro and HP Sure Click Pro) is effective upon activation and will continue for twelve (12) months thereafter ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the standard versions of HP Sure Click and HP Sure Sense at no additional cost with no future software updates or HP Support."

[4] Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[5] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[6] HP Wolf Security for Business requires Windows 10 and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features and OS requirements.

[7] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[9] HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[11] Sold separately or as an optional feature.

[14] Full-High Definition (FHD) content required to view FHD images.

[15] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[16] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[19] Availability may vary by country.

[21] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit <http://www.hpdaas.com/requirements>. Not applicable in China.

[32] HP Tamper Lock must be enabled by the customer or your administrator.

[46] Actual brightness will be lower with touchscreen.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Arc and vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. NVIDIA, the NVIDIA logo are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

