

Lenovo Chrome 100e G5 M89

Powered by the MediaTek Kompanio 540 processor, this Chromebook offers dependable, energy-efficient performance for everyday business use. With 8GB LPDDR5-6400 memory and up to 64GB SSD storage, professionals can seamlessly manage multiple browser tabs, spreadsheets, and collaboration applications at once, boosting productivity and minimizing interruptions. Moreover, a 50Wh rechargeable Li-ion battery with Rapid Charge Pro technology provides all-day power, supporting extended work sessions without frequent recharging.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

Dual 2W stereo speakers, enhanced with Waves MaxxAudio®, deliver rich, clear audio for virtual meetings and training sessions, enabling effective communication. The integrated dual-microphone array ensures precise voice capture during calls, even in shared or noisy work environments.

The 11.6" HD IPS display enhances the readability of documents and dashboards, helping to reduce eye strain during extended work sessions. Furthermore, the multi-touch capability allows professionals to easily navigate, zoom, scroll, and switch between documents or web applications using intuitive touch gestures.

The built-in 720p HD front camera enhances professional presence during virtual meetings, while the integrated privacy shutter provides added peace of mind when the camera is not in use.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo 65W USB-C AC Travel Adapter

- Ultraportable, lightweight design perfect for frequent commutes and travel
- Charge USB-C devices up to 65W. Universal travel plugs cover most regions and are easily replaceable
- Convenient carry pouch for travelers included



PN: 40AW0065WW GOA6N065WW 40AW0065EU-(EU plug)

Lenovo Go Wireless Multi-Device Mouse

- Compact ambidextrous design, programmable Utility Button on the side, default functions optimized for Teams calls
- Connects to up to 3 devices via 1x USB-C dongle, 2x Bluetooth 5.0; quick switch button to jump control across devices
- Comes with a blue optical sensor that tracks on most surfaces and wireless Qi or wired USB-C fast-chargeable battery



PN: 4Y51C21217

Lenovo Chrome 100e G5 M89



Performance

Processor MediaTek Kompanio 540
Operating System [*] ChromeOS
Graphics Arm Mali-G57 MC2 GPU (integrated)
Memory 4GB LPDDR5-6400, soldered 8GB LPDDR5-6400, soldered
Storage 64GB UFS 2.2 on systemboard
Audio [*] High Definition (HD) Audio, Smart Amplifier (AMP) 2W x2, optimized with Waves MaxxAudio Dual-microphone array
Camera [*] HD 720p, with privacy shutter
Battery 33.3Wh (up to 14.7 hr) or 50Wh (up to 22.5 hr) battery, Rapid Charge Pro
Power Adapter [*] 65W USB-C adapter, PD 3.0
Design
Display 11.6" HD (1366x768) IPS glossy 16:9 - 250nits, 50% NTSC, touch 11.6" HD (1366x768) IPS Anti-glare 16:9 - 250nits, 50% NTSC 12.2" WUXGA (1920x1200) IPS Anti-glare 16:10 - 300nits, 50% NTSC
Keyboard 6-row, backlight
Touchpad Mylar surface touchpad, 60.5 x 104 mm (2.38 x 4.09 inches)
Dimensions 288.9 x 210 x 18.5 mm (11.37 x 8.27 x 0.73 inches)

Weight Models with touch panel: starting at 1.26 kg (2.78 lbs) Models with non-touch panel: Starting at 1.22 kg (2.69 lbs)
Color Luna grey
Case material PC-ABS + 15% Talc + TPU (top), PC-ABS + 15% Talc + 50% PCR (bottom)

Connectivity

WLAN + Bluetooth [*] AMD RZ616, 802.11ax (Wi-Fi 6E), Bluetooth 5.3 Mediatek MT7925, 802.11be (Wi-Fi 7), Bluetooth 5.3
WWAN [*] 4G LTE CAT6*
Ports 2x USB-A (USB 5Gbps) 2x USB-C (USB 5Gbps), with USB PD 45-65W & Display Port 1x HDMI 1.4b 1x Headphone / microphone combo jack (3.5mm)
Docking Docking support via USB-C

Security & Privacy

Security Google Security Chip H1 Camera privacy shutter Kensington Nano Security Slot

Environmental

Material 50% PCC recycled plastic used in D cover 30% PCC recycled plastic used in keyboard keycaps and frame 90% PCC recycled plastic used in the battery and adapter enclosure pack Recycled aluminum keyboard bracket Recycled steel touchpad bracket 90% recycled sustainable content in packaging

Certifications

Green Certifications ENERGY STAR 9.0 EPEAT Gold Registered ErP Lot 6/26 TCO Certified, generation 10 RoHS compliant
Other Certifications ASTM F963* MIL-STD-810H military test passed TÜV Rheinland Low Blue Light (Software Solution)

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2026 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.