

ThinkPad L13 Gen 6 (Intel)

Built for mobility and designed with versatility in mind, this laptop leverages up to Intel® U Series Core Ultra 7 Processor to streamline heavy workloads while keeping energy use in check. With integrated Intel® AI Boost delivering up to 12 TOPS, it powers intelligent applications that support content creation, data analysis, and real-time collaboration with remarkable efficiency. Intel® graphics ensure fluid visuals for everything from video editing to presentations, while up to 32GB DDR5x memory enables seamless multitasking across design software, spreadsheets, and research tools without performance dips.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad L series laptops offer reliable performance and durability for modern professionals with powerful processors, robust security features, long battery life, and versatile connectivity options, ensuring productivity on-the-go.

Its vibrant 13.3" WUXGA display with 100% sRGB color accuracy offers crisp, true-to-life visuals ideal for creatives and presenters alike. The optional multi-touch screen enhances interactivity, while a range of modern ports and up to Wi-Fi® 7 ensure uninterrupted connectivity everywhere.

With up to 1TB SSD storage, professionals can carry large files and boot applications quickly. Discrete TPM 2.0 and a touch style fingerprint reader safeguard sensitive data, securing remote work for consultants, executives, and field-based teams.

Optimized for seamless web conferencing, it features a dual-microphone array that captures clear voice input and an HD 720p camera with fixed focus. A built-in privacy shutter ensures visual security between meetings and video calls.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

Lenovo Essential Wireless Combo Keyboard & Mouse Gen 2

- Embrace the freedom of a clutter-free and cable-free work setup.
- Ergonomically sculpted cups and low-profile island keys for maximum comfort.
- A 2.4 MHz receiver for a seamless keyboard and mouse connection.



PN: 4X31N50708 – 4X31N50757

ThinkPad L13 Gen 6 (Intel)

Performance

Processor

Intel U Series Core Ultra 5 / 7 Processor (Series 2)

AI PC Category*

AI PC

Operating System*

Windows 11 Pro or Home
Ubuntu Linux

NPU*

Integrated Intel AI Boost, up to 12 TOPS

Graphics

Intel Graphics (integrated)

Memory¹

16GB LPDDR5x-7467, soldered
32GB LPDDR5x-7467, soldered

¹Installed memory is actually LPDDR5x-8533 but runs as LPDDR5x-7467 due to platform limitation.

Storage²

One drive, up to 2TB M.2 2242 SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Elevoc Voice

Camera*

HD 720p, with privacy shutter
5.0MP + IR discrete, with privacy shutter, temporal noise reduction

Battery³

41Wh or 54.7Wh battery, up to 12.8 hr, Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁴

13.3" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC 3M DBEF5
- 400nits, 100% sRGB, Eyesafe
- 400nits, 100% sRGB, Eyesafe, touch

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio

84.7%

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

TrackPoint, Mylar or glass-like Mylar surface TrackPad
60 x 115 mm (2.36 x 4.53 inches)

Dimensions⁵

299.0 x 215.0 x 12.0/15.7 (front/rear), 18.95 (maximum) mm;
11.77 x 8.46 x 0.47/0.62 (front/rear), 0.75 (maximum) inches

⁵The system dimensions may vary depending on configurations.

Weight⁶

Starting at 1.21 kg (2.67 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

Aluminium (top), PC + 40% GF (bottom)

Connectivity

WLAN + Bluetooth*

Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

WWAN*

4G LTE CAT6 with embedded eSIM*

NFC

Near Field Communication*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 and DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

ThinkShield
Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*
Privacy Guard with Privacy Alert (software solution)

Manageability

System Management*⁷

Intel vPro Enterprise*

⁷Intel vPro offers a superset of DASH's defined capabilities.

Environmental

Material

50% recycled aluminium on top cover
50% PCC recycled on aluminium top cover top frame
50% PCC recycled on display cover bezel
30% PCC recycled on bottom cover
85% PCC recycled plastic used in key caps
90% PCC recycled plastic used in speaker enclosure
45% PCC recycled plastic + 5% OBP on dummy SMC and dummy SIM cover
25% OBP recycled on fan housing
12% recycled rare earth fan magnet
30% recycled rare earth speaker magnet
90% PCC recycled plastic used in slim GaN 65W adapters and standard 65W adapters
90% PCC recycled plastic used in the battery pack enclosure
90% recycled and/or sustainable content for packaging

Certifications

Green Certifications^{8 9 10}

ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified, generation 10
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹⁰EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.